Dimensions: [mm]

φ 26,3 ±0,3

WE 760308101309

Φ 16,96 ±0,3 Φ 24,48 ±0,5

0,49 ±0,2

25,0 ±2,0 5,0 ±2,0

10130

detail A

0,25

Φ

Scale - 1,5:1

B

RoHS COMPLIANT

 \bigcirc

HALOGEN

WURTH ELEKTRONIK


MORE THAN YOU EXPECT

REACh COMPLIANT

Schematic:

А


Recommended Hole Pattern: [mm]



Electrical Properties:

2 Inductance L 125 kHz/10 mA 10 Rated Current I _R AT = 40 K 1.5 0 Q-Factor Q 125 kHz/10 mA 20 0 Power Capability P V _{DC} = 20 V 20 0 DC Resistance R _{DC} @ 20 °C 350 0 DC Resistance R _{DC} @ 20 °C 450 5 Self Resonant Frequency I _{res} 19 1 1 Certification: RoHS Approval Conform or declared (EC)1907/200 Halogen Free Conform (JEDEC JS709B) 1 Halogen Free Conform [JEDEC JS709B] 40 °C; < 75 % RH Moisture Sensitivity Level (MSL) 1 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe 01.002 2022-05-09 DR Hu if not specified diffe					
Rated Current IR AT = 40 K 1.5 Q-Factor Q 125 kHz/10 mA 20 Power Capability P Vbc = 20 V 20 DC Resistance Rpc @ 20 °C 350 DC Resistance Rpc @ 20 °C 450 Self Resonant Frequency fres 19 19 Certification: RothS Approval Comform or declared (EC)1907/201 RothS Approval Conform or declared (EC)1907/201 Both Approval Conform or declared (EC)1907/201 Roth Conform (JEDEC JS709B) Halogen Free Conform (JEDEC JS709B) Halogen Free Conform (JEDEC JS709B) Halogen Free Conform (JEDEC JS709B) General Information: Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Mosture Sensitivity VE-WPCC Wireless Power WE-WPCC Wireless Power West cont Moster Sensore WE-WPCC Wireless Power West cont West cont	Unit	Tol.			
Q-Factor Q 125 kHz/10 mÅ 20 Power Capability P V _{DC} = 20 V 20 20 DC Resistance R _{DC} @ 20 °C 350 DC DC Resistance R _{DC} @ 20 °C 450 Self Resonant Frequency fms 19 Certification: Roth Approval Compliant (2011/65/EU82015/86 Reach Approval Conform or declared ([C)1907/201 Halogen Free Conform or declared ([C)1907/201 Halogen Free Conform [LEDEC JS709B] Halogen Free Conform [LEC 61249-2-21] Storage Conditions (in original packaging) < 40 °C ; < 75 % RH Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe VCMe 001.002 DOE 205-00 DN IS0 2768-1m Mostor WE-WPCC Wireless Power WE-WPCC Wireless Power Mostor Coll Mostor Coll	μH	±10%			
Power Capability P V _{DC} = 20 V 20 DC Resistance R _{DC} @ 20 °C 350 0 DC Resistance R _{DC} @ 20 °C 450 350 0 Self Resonant Frequency Ites 19 19 19 19 Certification: RoHS Approval Compliant (2011/65/EU82015/86 REACh Approval Compliant (2011/65/EU82015/86 Scale - 2:1 RoHS Approval Conform or declared [[EC]1907/200 Halogen Free Conform or declared [[EC]1907/200 Halogen Free Conform (JEDEC JS709B) Halogen Free Conform [IEC 61249-2:21] Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Mode to Conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe WE-WPCC Wireless Power WE-WPCC Wireless Power	A	max.			
DC Resistance R _{DC} @ 20 °C 350 DC Resistance R _{DC} @ 20 °C 450 Self Resonant Frequency fres 19 Certification: Compliant [2011/65/EU82015/86 RACh Approval Compliant [2011/65/EU82015/86 REACh Approval Compliant [2011/65/EU82015/86 REACh Approval Conform or declared [[EC]1907/201 Halogen Free Conform (JEDEC JS709B] Halogen Free Conform (JEDE CJS709B] Halogen Free Conform (JEDE CJS709B) Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Moderations ME-WPCC Wireless Power WE-WPCC Wireless Power Transfer Receiver Coil Testence		typ.			
DC Resistance Rpcc @ 20 °C 450 Self Resonant Frequency 1 19 Certification: RoHS Approval Compliant [2011/65/EU82015/86 REACh Approval Conform or declared [(EC)1907/201 Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC 4249-2-21] Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	W	typ.			
DC Resistance Hoc @ 20 °C 450 Self Resonant Frequency fres 19 Certification: RoHS Approval Compliant [2011/65/EU82015/86 REACh Approval Comform or declared [[EC]1907/200 Halogen Free Conform or declared [[EC]1907/200 Halogen Free Conform [IEC 61249-2-21] General Information: Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	mΩ	typ.			
Certification: Compliant [2011/65/EU82015/86 REACh Approval Comform or declared [(EC)1907/200 Halogen Free Conform (JEDEC JS709B) Halogen Free Conform [JEDE C S1709B] Halogen Free Conform [JEDE C S1709B] Halogen Free Conform [JEDE C S1709B] Halogen Free Conform [JED C 61249-2-21] General Information: Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) A 0 °C ; < 75 % RH	mΩ	max.			
Scale - 2:1 RoHS Approval Compliant [2011/65/EU82015/86 REACh Approval Conform or declared [(EC)1907/200 Halogen Free Conform (JEDEC JS709B) Halogen Free Conform [JEC 61249-2-21] General Information: Operating Temperature Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	MHz	typ.			
REACh Approval Conform or declared [(EC)1907/200 Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] General Information: Operating Temperature Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH					
Scale - 2:1 Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEC 61249-2-21] General Information: Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	63]				
the detonik also Griff & Co. KG the detonik also Griff &)06]				
General Information: Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH					
Operating Temperature -20 up to +105 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH					
Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe OECKED REVISION OECKED REVISION OUT.002 2022-05-09 DIN ISO 2768-1m PROJECTION DESCRIPTION WE-WPCC Wireless Power Transfer Receiver Coil OPER CODE 760209101200 CODE					
Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified diffe Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2">Colspan="2"Colsp					
CHECKED REVISION DATE (YYY-MM-DD) GENERAL TOLERANCE PROJECTION CME 001.002 2022-05-09 DIN ISO 2768-1m PROJECTION DESCRIPTION WE-WPCC Wireless Power Image: Constraint of the constraint of	erentlv				
Auth Elektronik elSos GrabH & Co. KG MC & Inductive Solutions ax-Eyth-Str. 1					
With Elektronik elSos GmbH & Co. KG MC & Inductive Solutions WE-WPCC Wireless Power Transfer Receiver Coil		<u> </u>			
WE-WPCC Wireless Power Image: Constraint of the solutions Inth Elektronik elSos GmbH & Co. KG Transfer Receiver Coil URDER CODE Xx Eytin-Str. 1 Transfer Receiver Coil Transfer Receiver Coil	€#	⊕-			
th Elektronik elSos GmbH & Co. KG C & Inductive Solutions K-Eyth-Str. 1		<u> </u>			
Irth Elektronik elSos GmbH & Co. KG IC & Inductive Solutions w-Eyth-Str. 1					
	ORDER CODE				
1638 Waldenburg	760308101309				
		PAGE			
sos@we-online.com Ø 26 x 0.5 mm eiSos Valid	Valid 1/6				


This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel



Q-Factor vs. Frequency:

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equivalent is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information network etc.. Wurth Elektronik elSos GmbH & Co KG must be information intended to use is electronic component which is used in electrical circuits there adjust high standard is especially executed an electronic component which is used in electrical circuits there are electrical circuits ther

Typical Inductance vs. Frequency Characteristics:



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equivalent is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information network etc.. Wurth Elektronik elSos GmbH & Co KG must be information intended to use is electronic component which is used in electrical circuits there adjust high standard is especially executed an electronic component which is used in electrical circuits there are electrical circuits ther

Classification Wave Soldering Profile:



---- max temperature procedure

Classification Wave Soldering Profile:

Profile Feature		Pb-Free Assembly	Sn-Pb Assembly
Preheat Temperature Min	T _{s min}	100 °C	100 °C
Preheat Temperature Typical	T _{s typical}	120 °C	120 °C
Preheat Temperature Max	T _{s max}	130 °C	130 °C
Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$	t _s	70 seconds	70 seconds
Ramp-up Rate	ΔT	150 °C max.	150 °C max.
Peak Temperature	Т _р	250 °C - 260 °C	235 °C - 260 °C
Time of actual peak temperature t _p		max. 10 seconds max. 5 seconds each wave	max. 10 seconds max. 5 seconds each wave
Ramp-down Rate, Min		~ 2 K/ second	~ 2 K/ second
Ramp-down Rate, Typical		~ 3.5 K/ second	~ 3.5 K/ second
Ramp-down Rate, Max		~ 5 K/ second	~ 5 K/ second
Time 25 °C to 25 °C		4 minutes	4 minutes

refer to EN61760-1:2006

	ROHS ROHS ROHS REAC REAC HALGEN		CHECKED	REVISION 001.002	DATE (YYYY-MM-DD) 2022-05-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	₩ -	
			WE-WPCC Wireless Power							
			Transf	er Rece	iver Coil		ORDER CODE	: 308101309		
	./-	MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type Ø 26 x 0.5 mn	n		BUSINESS UNIT eiSos	status Valid		PAGE 4/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-WPCC of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, as the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.

Cleaning and Washing:

Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- · Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- Due to heavy weight of the components, strong forces and high accelerations may have the effect to damage the electrical connection
 or to harm the circuit board and will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

			CHECKED	REVISION 001.002	DATE (YYYY-MM-DD) 2022-05-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	-	€-	
	ROMS COMPLIANT COMPLIANT HALOGEN FREE			WE-WPCC Wireless Power							
ELE		WURTH ELEKTRONIK	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Transf	Transfer Receiver Coil				ORDER CODE 760308101309		
		MORE THAN YOU EXPECT	Tel. +44 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com	size/type Ø 26 x 0.5 mr	n		BUSINESS UNIT eiSos	status Valid		1	PAGE 5/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, ship control, train control, tra

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

		CHECKED	REVISION 001.002	DATE (YYYY-MM-DD) 2022-05-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	_ -			
	Rents COMPLIANT HALOGEN COMPLIANT REACH FREE WÜRTH ELEKTRONIK MAX-5yth-Str. 1 74638 Waldenburg Germany Germany			WE-WPCC Wireless Power							
			Transf	er Rece	iver Coil		ORDER CODE	308101309	_		
		MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type Ø 26 x 0.5 mm	n		BUSINESS UNIT eiSos	status Valid		PAGE 6/6	

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be information network etc... Wūrth Elektronik elSos GmbH & Co KG must be information network etc... Wūrth Elektronik elSos GmbH & Co KG must be information network etc... Wūrth Elektronic experiment severe personal injury or death, unless the parties have executed an agreement specifically governing such use, in addition, sufficient reliability evaluation checks for safety must be performation network etc... Wūrth Elektronic component which is used in developed for use age before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in developed relicital circuits that require high safety and reliability evaluation checks for safety must be performed on every electronic component which is used in developed relicital circuits that require high safety and reliability functions or performance.