




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.26 ohms max.
D.C. RESISTANCE	4-6 @20°C	0.46 ohms max.
D.C. RESISTANCE	6-5 @20°C	0.30 ohms max.
D.C. RESISTANCE	7-9 @20°C	1.36 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.20 ohms max.
D.C. RESISTANCE	10-11 tie(9+10,11+12), @20°C	0.04 ohms max.
INDUCTANCE	1-3 10kHz, 100mV, Ls	1.05mH ±6%
SATURATION CURRENT	1-3 20% rolloff from initial	2.2A
LEAKAGE INDUCTANCE	1-3 tie(7+8+9+10+11+12),100kHz, 100mV, Ls	4µH max.
DIELECTRIC	1-12 tie(3+4,7thr12), 3750VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(3-1):(4-6)	8:1
URNS RATIO	(3-1):(6-5)	13.33:1
URNS RATIO	(3-1):(7-9)	2.35:1
URNS RATIO	(3-1):(9-8)	20:1
URNS RATIO	(3-1):(11-10), tie(9+10,11+12)	4:1



Customer to tie terminals 9+10 and 11+12 on PC board
 Application of the transformer allows for the leadwires between terminals 9&10, 11&12 to solder bridge.

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60335-1

- Reinforced insulation for a primary circuit at a working voltage of 500Vrms, 700Vpeak, Pollution Degree 2.

Designed to comply with the following requirements as defined by IEC61558-2-16, and EN61558-2-16:

- Reinforced insulation for a primary circuit at a working voltage of 500Vrms, 700Vpeak (operating frequency of <1MHz), Pollution Degree 2.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750845740
DATE	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	NWU	www.we-online.com/midcom		SPECIFICATION SHEET 1 OF 1	
REV.	02				
DATE	2022/8/16				