


QUARTZ CRYSTALS AND MATCHING CAPACITORS

WE-XTAL, WCAP-CSRF, WCAP-CSGP



Model:
HC49/4HSMX | 13.4 x 4.9 mm
HC49 | 11.05 x 4.65 mm
CFPX-104 | 5.0 x 3.2 mm
CFPX-180 | 3.2 x 2.5 mm
CFPX-217 | 3.2 x 1.5 mm
WATCH | 2.0 x 6.0 mm
CFPX-218 | 2.5 x 2.0 mm

IQXC-42 | 2.0 x 1.6 mm
IQXC-25 | 2.0 x 1.2 mm
IQXC-26 | 1.6 x 1.2 mm
IQXC-90 | 1.6 x 1.0 mm
IQXC-240 | 1.2 x 1.0 mm
IQXC-146 | 1.2 x 1.0 mm



more details online

QUARTZ CRYSTALS						CAPACITORS		
830 030 798 Frequency: 3.68640 MHz Specification: 30/50/-40 to 85 °C / 18 pF	830 059 523 Frequency: 12.2880 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 055 293 Frequency: 14.74560 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 054 236 Frequency: 0.032768 MHz Specification: 20/-/-/ 6 pF	830 069 493 Frequency: 24.0 MHz Specification: 15/20/-40 to 85 °C / 10 pF	830 081 609 Frequency: 25.0 MHz Specification: 10/20/-40 to 85 °C / 8 pF	885 392 005 047 Capacity: 3.9 pF Voltage: 50 V Size: 0402	885 392 005 014 Capacity: 9.0 pF Voltage: 50 V Size: 0402	885 392 005 114 Capacity: 22.0 pF Voltage: 50 V Size: 0402
830 028 392 Frequency: 4.91520 MHz Specification: 30/50/-20 to 70 °C / 18 pF	830 106 163 301 Frequency: 13.560 MHz Specification: 20/30/-40 to 85 °C / 16 pF	830 055 951 Frequency: 16.0 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 009 678 Frequency: 0.032768 MHz Specification: 20/-/-/ 12.5 pF	830 069 494 Frequency: 25.0 MHz Specification: 15/20/-40 to 85 °C / 10 pF	830 108 161 001 Frequency: 27.0 MHz Specification: 10/20/-40 to 85 °C / 8 pF	885 392 005 051 Capacity: 4.3 pF Voltage: 50 V Size: 0402	885 392 005 106 Capacity: 10.0 pF Voltage: 50 V Size: 0402	885 012 006 034 Capacity: 22.0 pF Voltage: 25 V Size: 0603
830 050 510 Frequency: 8.0 MHz Specification: 30/50/-40 to 85 °C / 18 pF	830 072 403 Frequency: 14.74560 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 100 965 009 Frequency: 16.0 MHz Specification: 10/20/-40 to 85 °C / 16 pF	830 014 219 B Frequency: 0.032768 MHz Specification: 20/-/-/ 6 pF	830 108 212 609 Frequency: 26.0 MHz Specification: 10/15/-40 to 85 °C / 8 pF	830 108 161 301 Frequency: 32.0 MHz Specification: 10/20/-40 to 85 °C / 8 pF	885 392 005 013 Capacity: 5.6 pF Voltage: 50 V Size: 0402	885 012 006 032 Capacity: 10.0 pF Voltage: 25 V Size: 0603	885 012 006 095 Capacity: 22.0 pF Voltage: 50 V Size: 0603
830 003 210 Frequency: 12.0 MHz Specification: 30/50/-20 to 70 °C / 18 pF	830 059 531 Frequency: 24.5760 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 107 878 109 Frequency: 16.0 MHz Specification: 30/50/-40 to 125 °C / 12 pF	830 002 997 B Frequency: 0.032768 MHz Specification: 20/-/-/ 12.5 pF	830 108 212 709 Frequency: 27.120 MHz Specification: 10/15/-40 to 85 °C / 8 pF	830 107 088 501 Frequency: 0.032768 MHz Specification: 20/-/-/ 6 pF	885 012 005 054 Capacity: 6.8 pF Voltage: 50 V Size: 0402	885 012 007 028 Capacity: 10.0 pF Voltage: 25 V Size: 0805	885 012 007 030 Capacity: 22.0 pF Voltage: 25 V Size: 0805
830 036 034 Frequency: 16.0 MHz Specification: 30/50/-40 to 85 °C / 18 pF	830 108 313 809 Frequency: 8.0 MHz Specification: 30/50/-40 to 85 °C / 12 pF	830 055 299 Frequency: 25.0 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 063 334 Frequency: 25.0 MHz Specification: 20/20/-40 to 85 °C / 10 pF	830 108 212 909 Frequency: 32.0 MHz Specification: 10/15/-40 to 85 °C / 8 pF	830 066 198 Frequency: 0.032768 MHz Specification: 20/-/-/ 9 pF	885 012 006 031 Capacity: 6.8 pF Voltage: 25 V Size: 0603	885 392 005 127 Capacity: 12.0 pF Voltage: 50 V Size: 0402	885 392 005 116 Capacity: 27.0 pF Voltage: 50 V Size: 0402
830 003 044 B Frequency: 2.45760 MHz Specification: 20/50/-10 to 60 °C / 30 pF	830 108 338 709 Frequency: 10.0 MHz Specification: 20/50/-40 to 105 °C / 12 pF	830 105 863 709 Frequency: 25.0 MHz Specification: 30/30/-40 to 85 °C / 12 pF	830 069 390 Frequency: 32.0 MHz Specification: 20/20/-40 to 85 °C / 10 pF	830 059 627 Frequency: 38.40 MHz Specification: 15/30/-30 to 85 °C / 10 pF	830 108 131 601 Frequency: 38.40 MHz Specification: 7/15/-30 to 85 °C / 5 pF	885 012 007 027 Capacity: 6.8 pF Voltage: 25 V Size: 0805	885 012 005 056 Capacity: 15.0 pF Voltage: 50 V Size: 0402	885 012 006 035 Capacity: 33.0 pF Voltage: 25 V Size: 0603
830 055 663 Frequency: 8.0 MHz Specification: 20/30/-40 to 85 °C / 18 pF	830 108 206 909 Frequency: 12.0 MHz Specification: 10/20/-40 to 85 °C / 8 pF	830 108 340 909 Frequency: 26.0 MHz Specification: 10/20/-40 to 105 °C / 12 pF	830 108 208 809 Frequency: 50.0 MHz Specification: 10/10/-20 to 70 °C / 10 pF	830 108 213 209 Frequency: 40.0 MHz Specification: 10/15/-40 to 85 °C / 8 pF	830 108 049 101 Frequency: 48.0 MHz Specification: 10/10/-30 to 85 °C / 8 pF	885 392 005 081 Capacity: 7.5 pF Voltage: 50 V Size: 0402	885 012 006 033 Capacity: 15.0 pF Voltage: 25 V Size: 0603	885 012 005 059 Capacity: 47.0 pF Voltage: 50 V Size: 0402
830 055 999 Frequency: 12.0 MHz Specification: 30/30/-40 to 85 °C / 18 pF	830 061 647 Frequency: 12.0 MHz Specification: 20/30/-40 to 85 °C / 12 pF	830 053 099 Frequency: 27.120 MHz Specification: 10/10/-20 to 70 °C / 10 pF	830 059 585 Frequency: 20.0 MHz Specification: 15/20/-40 to 85 °C / 10 pF	830 050 789 Frequency: 0.032768 MHz Specification: 20/-/-/ 12.5 pF	830 107 834 801 Frequency: 0.032768 MHz Specification: 20/-/-/ 6 pF	885 392 005 088 Capacity: 8.2 pF Voltage: 50 V Size: 0402	885 012 004 007 Capacity: 18.0 pF Voltage: 25 V Size: 0201	885 012 006 036 Capacity: 47.0 pF Voltage: 25 V Size: 0603

PASSIVE COMPONENTS | ELECTROMECHANICAL COMPONENTS | POWER MODULES | OPTOELECTRONICS | THERMAL MANAGEMENT | CUSTOM MAGNETICS | AUTOMOTIVE | WIRELESS CONNECTIVITY & SENSORS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. ©2025

**ALL PRODUCTS
EX STOCK!**