

WE CABIN DISPLAY i7

Intelligent HMI Solutions



WEcabin Display i7 is an intelligent HMI solution for mobile machines and commercial vehicles developed by Würth Elektronik ICS.

Description:

- Robust housing for the use in tough environmental conditions
- High processing power and memory size
- High optical performance ensures good readability in all lighting conditions
- Optical bonding enhance visibility and reliability
- Easy to customise for individual design of graphical user interface (GUI) with WEcabin Designer.

Technical data

General information	
Processor	Dual Core ARM Cortex-A7
RAM	1 GB DDR3
Clock frequency	650 MHz
Flash memory	8 GB
FRAM	64 Kb
Real time clock	Rechargeable lithium battery
Operating temperature	-30 °C to +70 °C
Storage temperature	-40 °C to +85 °C
Ingress protection	IP 66 IP69K (front part) for the version without buttons
Operating voltage	8 V to 32 V DC
Power consumption	250 mA at 24 V
Stand-by mode consumption	2 mA
Housing	POLIMID PA6 UV
Connectors	AMP SUPERSEAL 34 Way connector, 60 pins connectors for Expansion Modules
Dimensions max.	221.5 x 143.5 x 47 mm
Signaling	Internal buzzer (90 dB)
Weight	900 g (without buttons)

Interfaces

CAN bus	2 x CAN 2.0B	11/29 Bits extended address identifier
	Baud rate	50 kBit/s to 1000 kBit/s (250 kBit/s default value)
Ethernet	1 x 10/100 Mbit/s	
USB	2 x 2.0 Host full speed	12 MB, 100 mA
RS-485 / RS-232	1 x up to 150 kbd	

Inputs & outputs overview

4	Digital inputs	High side 0 – 24 V
4	Digital outputs	Low side 500 mA at 24 V

Display specifications

Display	7" TFT LCD 16:9
Resolution	1024 x 600 WGVA 128 PPI
Backlight	LED
Brightness	500 cd/m ²
ON / OFF LED	Included
Orientation	Landscape or portrait programmable mode
Colors	24 bit
Contrast ratio	600:1
Cover glass	3.0 mm thickness tempered glass
TFT installation	Liquid optical bonding


Physical inputs

Touch Interface	PCAP multi touch screen
Buttons	2 x 5 silicon soft keys backlighted (optional)

Sensors

3-axis digital accelerometer	Optional
Temperature sensor	
Light sensor	

Hardware map




TE Connectivity AMP SUPERSEAL 34 Way Connector
Part No. 4-1437290-0v



TE Connectivity AMP SUPERSEAL 1.0 mm Connector
Receptacle Contact Assembly, AWG 16
Part No. 3-1447221-3

TE Connectivity AMP SUPERSEAL 1.0 mm Connector
Receptacle Contact Assembly, AWG 20
Part No. 3-1447221-4



Pinout of the connector

Pin assignment

Pin	Signal	Description
1	GND	Ground
2	IN2	Digital input 2
3	IN1	Digital input 1
4	USB1_GND	USB 1 Ground
5	RX_N	Receive negative
6	RX_P	Receive positive
7	TX_N	Transmit negative
8	TX_P	Transmit positive
9	VBAT	Power supply battery
10	IN4	Digital input 4
11	IN3	Digital input 3
12	GND	Ground
13	USB2_GND	USB 2 ground
14	VBUS2	USB 2 +5 V DC
15	VBUS1	USB 1 +5 VDC
16	GND	Ground
17	V_SW	Ignition voltage
18	OUT1	Digital output 1
19	OUT2	Digital output 2
20	CAN2_H	CAN 2 High (WEcabin Designer CAN 1)
21	CAN1_H	CAN 1 High (WEcabin Designer CAN 0)
22	USB2H_DM	USB 2 Data minus
23	USB1_DM	USB 1 Data minus
24	RXD	Serial port received data
25	GND24	Power supply ground
26	NC	Reserved, not connected
27	OUT3	Digital output 3
28	OUT4	Digital output 4
29	CAN2_L	CAN 2 Low (WEcabin Designer CAN 1)
30	CAN1_L	CAN 1 Low (WEcabin Designer CAN 0)
31	USB2H_DP	USB 2 Data plus
32	USB1_DP	USB 1 Data plus
33	TXD	Serial port transmitted data
34	SHIELD	Shield protection

Qualification

Test methods		
EMC	Automotive	ECE R10
EMC	Earth Moving and Construction Machinery	ISO 13766-1
EMC	Agricultural and Forestry Machinery	ISO 14982
Vibration & Shock	–	EN 60068-2
Ingress protection	IP66K IP69K (front part) for the version without buttons	ISO 20653
Salt spray	–	ISO 9227
Temperature	–	EN 60068-2
RED	–	ETSI EN 301-489 ETSI EN 300 328 EN 61010 EN 62311




Programming environment

Software	
Operating system	Linux Embedded
Application programming	WEcabin Designer CoDeSys™ PLC (optional) QT™ (optional)

Dimensions & Mounting possibilities

Dimensions	
Front length	221.5 mm
Front height	143.5 mm
Rear length	208 mm
Rear height	130 mm
Width	47 mm

Mounting possibilities	
In-dash mounting	Fixing supports provided
Out-dash mounting	RAM Mount™ (type C)



Available version

Version	i7 Standard
Processor	Dual Core ARM Cortex A7
Memory	1 GB RAM, 8 GB Flash
FRAM	64 KB
Capacitive touch screen	✓
Optical bonding	✓
7" Display, 1.024 x 600 (portrait/ landscape), 500 cd/m ²	✓
Light sensor on/off LED	✓
CAN bus	2
USB 2.0 port	2
Ethernet	✓
RS-485 / RS-232	✗
4 x digital inputs	✓
4 x digital outputs	✓
Accelerometer, temperature sensor	✗
Keyboard (2 x 5 buttons)	Optional

Part number	Description
X03441	i7 Standard
X03442	i7 Standard with buttons

**CONTACT US**

Würth Elektronik ICS GmbH & Co. KG
Intelligent Power & Control Systems

ics@we-online.com · www.we-online.com/ics