




# **Dimensions: [mm]**












## **Recommended Land Pattern: [mm]**



## **Schematic:**



## **Dimensions:**

| Properties |   | Value | Unit |
|------------|---|-------|------|
| Height     | Н | 4.3   | mm   |

| (3) (A) (A)                                 | ·   | CHECKED                   | REVISION 001.002 | DATE (YYYY-MM-DD)<br>2020-12-10 | GENERAL TOLERANCE DIN ISO 2768-1m |                 | PROJECTION METHOD | <del>1</del> - |
|---|---|---------------------------|------------------|---------------------------------|-----------------------------------|-----------------|-------------------|----------------|
| ROHS REACH HALOGEN COMPLIANT COMPLIANT FREE |   | DESCRIPTION WS-TA         | SV SMT           | Tact Swit                       | ch                                |                 |                   |                |
|   | Würth Elektronik elSos GmbH & Co. KG<br>EMC & Inductive Solutions<br>Max-Eyth-Str. 1<br>74638 Waldenburg<br>Germany |                           |                  |                                 |                                   | ORDER CODE      | 111043826         |                |
| WÜRTH ELEKTRONIK                            | Gentary Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com  | SIZE/TYPE<br>6.0 x 3.5 mm |                  |                                 | eiCan                             | status<br>Valid |                   | PAGE<br>1/7    |

# **Material Properties:**

| Cover Material               | Stainless Steel |
|------------------------------|-----------------|
| Actuator Material            | LCP             |
| Actuator Flammability Rating | UL94 V-0        |
| Actuator Color               | White           |
| Frame Material               | LCP             |
| Frame Flammability Rating    | UL94 V-0        |
| Frame Color                  | Black           |
| Contact Material             | Stainless Steel |
| Contact Plating              | Silver          |
| Terminal Material            | Copper Alloy    |
| Terminal Plating             | Silver          |

# **Electrical Properties:**

| Properties                            |                  | Test conditions | Value | Unit   | Tol. |
|---------------------------------------|------------------|-----------------|-------|--------|------|
| Rated Current                         | I <sub>R</sub>   |                 | 50    | mA     |      |
| Rated Voltage                         | V <sub>R</sub>   |                 | 12    | V (DC) |      |
| Contact Resistance Initial            | R                |                 | 100   | mΩ     | max. |
| Contact Resistance After Life<br>Test | R                |                 | 1     | Ω      | max. |
| Insulation Resistance                 | R <sub>ISO</sub> | 500 V (DC)      | 100   | ΜΩ     | min. |
| Withstanding Voltage                  |                  | 1 min           | 250   | V (AC) |      |
| Bounce                                |                  |                 | 10    | ms     | max. |

## **Mechanical Properties:**

| Properties         | Test conditions  | Value | Unit   | Tol.   |
|--------------------|------------------|-------|--------|--------|
| Operation Force    |                  | 260   | g      | ±70g   |
| Electrical Life 1) | 50 mA/ 12 V (DC) | 30000 | Cycles |        |
| Stroke             |                  | 0.25  | mm     | ±0.1mm |


<sup>1)</sup> Cycle - Return to the original position

## **General Information:**


| Operating Temperature                      | -40 up to +85 °C   |
|--|--------------------|
| Storage Conditions (in original packaging) | < 40 °C; < 75 % RH |
| Moisture Sensitivity Level (MSL)           | 1                  |
| Washable                                   | No                 |


## **Certification:**


| RoHS Approval  | Compliant [2011/65/EU&2015/863]     |
|----------------|-------------------------------------|
| REACh Approval | Conform or declared [(EC)1907/2006] |
| Halogen Free   | Conform [IEC 61249-2-21]            |



## Packaging Specification - Tape and Reel: [mm]










| A0   | B0   | W         | T    | T1   | T2   | K0   | P0   | P1   | P2   | D0        | D1   | E1   | E2    | F     | Tape Type 2a | VPE / packaging unit |
|------|------|-----------|------|------|------|------|------|------|------|-----------|------|------|-------|-------|--------------|----------------------|
| typ. | typ. | $\pm 0,3$ | ref. | ref. | typ. | typ. | ±0,1 | ±0,1 | ±0,5 | +0,1/-0,0 | min. | ±0,1 | min.  | ±0,05 |              | pcs.                 |
| 3,80 | 8,50 | 16,00     | 0,35 | 0,10 | 4,75 | 4,30 | 4,00 | 8,00 | 2,00 | 1,50      | 1,50 | 1,75 | 14,25 | 7,50  | Polystyrene  | 1800                 |

## Packaging Specification - Reel: [mm]





| A<br>(mm) | B<br>(mm) | C<br>(mm) | D<br>(mm) | N<br>(mm) | W1<br>(mm) | W2<br>(mm) | W3<br>(mm) | W3<br>(mm) | Material    |
|-----------|-----------|-----------|-----------|-----------|------------|------------|------------|------------|-------------|
| ± 2,0     | min.      | min.      | min.      | min.      | + 2,0      | max.       | min.       | max.       |             |
| 330,00    | 1,50      | 12,80     | 20,20     | 60,00     | 16,40      | 22,40      | 15,90      | 19,40      | Polystyrene |



 Pull-of force

 Tape width
 16 mm
 0,1 N - 1,3 N



Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg

Germany
Tel. +49 (0) 79 42 945 - 0
www.we-online.com
eiSos@we-online.com

ORDER CODE
434111043826

# **Classification Reflow Profile for SMT components:**



## **Classification Reflow Soldering Profile:**

| Profile Feature                                      |                    | Value                           |
|--|--------------------|---------------------------------|
| Preheat Temperature Min                              | T <sub>s min</sub> | 150 °C                          |
| Preheat Temperature Max                              | T <sub>s max</sub> | 200 °C                          |
| Preheat Time $t_s$ from $T_{s  min}$ to $T_{s  max}$ | t <sub>s</sub>     | 60 - 120 seconds                |
| Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )     |                    | 3 °C/ second max.               |
| Liquidous Temperature                                | T <sub>L</sub>     | 217 °C                          |
| Time $t_L$ maintained above $T_L$                    | t <sub>L</sub>     | 60 - 150 seconds                |
| Peak package body temperature                        | T <sub>p</sub>     | $T_p \le T_c$ , see Table below |
| Time within 5°C of actual peak temperature           | t <sub>p</sub>     | 20 - 30 seconds                 |
| Ramp-down Rate (T <sub>P</sub> to T <sub>L</sub> )   |                    | 6 °C/ second max.               |
| Time 25°C to peak temperature                        |                    | 8 minutes max.                  |

refer to IPC/ JEDEC J-STD-020E

# Package Classification Reflow Temperature (T<sub>c</sub>):

| Properties  | Volume mm³<br><350            | Volume mm <sup>3</sup><br>350-2000 | Volume mm³ >2000 |
|---|-------------------------------|------------------------------------|------------------|
| PB-Free Assembly I Package Thickness<br>< 1.6 mm        | 260 °C                        | 260 °C                             | 260 °C           |
| PB-Free Assembly I Package Thickness<br>1.6 mm - 2.5 mm | 260 °C                        | 250 °C                             | 245 °C           |
| PB-Free Assembly I Package Thickness<br>> 2.5 mm        | 250 °C                        | 245 °C                             | 245 °C           |
| Applied cycles  | Only 2 times reflow possible. |                                    |                  |

refer to IPC/ JEDEC J-STD-020E

| <b>3 6 8</b>       |   | CHECKED                   | 001.002 |           | PROJECTION METHOD |                 |           |             |
|--------------------|---|---------------------------|---------|-----------|-------------------|-----------------|-----------|-------------|
| ROHS REACH HALDGEN | Würth Elektronik elSos GmbH & Co. KG  | WS-TA                     | SV SMT  | Tact Swit | 2000 2005         |                 |           |             |
|                    | EMC & Inductive Solutions<br>Max-Eyth-Str. 1<br>74638 Waldenburg<br>Germany |                           |         |           |                   | 4341            | 111043826 |             |
| WÜRTH ELEKTRONIK   | Tel. +49 (0) 79 42 945 - 0<br>www.we-online.com<br>eiSos@we-online.com      | SIZE/TYPE<br>6.0 x 3.5 mm |         |           | eiCan             | status<br>Valid |           | PAGE<br>4/7 |

## **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of Tact switch of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This mechanical component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- Mechanical components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
  specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Prevent any damage or scratches on the switch, especially on the actuator.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the
  authority of the customer. All technical specifications for standard products also apply to customer specific products.

#### **Product Specific:**

## Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- Please keep our switch at delivery original position before and during the soldering process.
- Design the right angle part with consideration of the wave soldering process so that the parts will not touch the soldering wave during
  the soldering process or protect the switch part with cover fixture. Melting of the switch might cause malfunction.

#### **Cleaning and Washing:**

If a series is washable, the general information section in the datasheet will contain the washability guidelines. Should there be no
information regarding washability, the product has not been constructed to withstand a washing process. Washing agents used during
the production to clean the customer application might damage or change the characteristics of the component, body, pins and/or
termination. Washing agents may have a negative effect on the long-term functionality of the product.

If the parts are washable, hermetic:

- Cleaning agents that are used to clean the customer applications may damage or change the characteristics of the component, body, pins and termination.
- Please do not immerse any washable products into water or cleaning agents or put them in locations exposed to water completely.
- Do not clean washable series immediately after soldering. The cleaning agent may be absorbed into the switch through respiration while
  the switch cools.
- Please do not press actuator or change status /position during the cleaning and washing process.
- Using a brush during the cleaning process may deform function relevant areas. Therefore, we do not recommend using a brush during
  the PCB cleaning process.

#### **Potting and Coating:**


If the product is potted in the customer application, the potting material may shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the body, pins or termination. Expansion could damage the components.
We recommend a manual inspection after potting or coating to avoid these effects.

## **Storage Conditions:**


- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- For a moisture sensitive component, the storage condition in the original packaging is defined according to IPC/JEDEC-J-STD-033. It is
  also recommended to return the component to the original moisture proof bag and reseal the moisture proof bag again.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

## Handling:

- In the case a product requires particular handling precautions, in addition to the general recommendations mentioned here below, these
  will appear on the product datasheet.
- Do not repeatedly operate the switch with excessive force. It may damage or deform the switch resulting in malfunction.
- Please set up the switch in such a way that the actuator will operate in a straight vertical line. A decrease in the lifetime of the switch
  may result if the actuator is pressed off-center or from an angle. This might cause function errors or broken actuators, especially for
  heights over 7.0 mm.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.



These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



## **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

#### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

### 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

