
5.0 5.0	1_0_0	. 7.4 .	9.80 6.20 4.15 2.60 1.30 97 97		L: LCP G UL94-V0 COPPER ALLOY MPED IELECTIVE GOLD I PLATED	A
+ ² ^{€°0}	0.9 2.45 4.6 1S Compliant		PCB EDGE PCB LAYOUT - COMPONEN TOLERANCE: ±0.05m	- OTHER PINS 1A MAX WORKING VOLTAGE: 3 INSULATION RESISTAN	REE AND ROHS & corresponding ground PIN) 1.8A MAX 30 V NCE: >1000 MΩ ANDING VOLTAGE: 750 VAC/MIN ΣΕ: 30 mΩ MAX 964	В
			$x = \frac{1}{2} = $			
			.XX = ⁺ / ₂ 0.15			
		APPROVAL: NPr		DESCRIPTION: MICRO USB 2.0 SMT TYPE B	3 5 CONTACTS - WR-COM SIZE	[≣] D
P	31-JUL-15 GENERAL UPD		SCALE: SHEET: 1/3	WEDI DADT NO: 620 405 426 924	A4	4
0 REV	31-OCT-14 GENERAL UPD DATE FILE	ATE AS BY	DRAW: AS	WERI PART NO: 629 105 136 821	~ -	*



1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В					SCALE:			Р
A	10-SEP-14	PDF	QL		SHEET: 3/3	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			