	1	2	3	4	5	
5.0 4.37 1 4.38 1 4.39 1 4.30			3.0±0.0	25 1.27 TECHNICAL CHAI MATERIAL INSULATOR: LCP FLAMABILITY RAY COLOR: BLACK CONTACT MATEFI CONTACT TYPE: CONTACT TYPE: CONTACT PLATIN QUALITY CLASS:	FING: UL94-V0 RIAL: COPPER ALLOY STAMPED IG: TIN	Α
TAPE AND REEL WITH CAP DIMENSION $A \pm 0.15$ 0.64 ± 0.1 1 2.0 1 1 1 1 1 1 1 2.0 1 1 2.0 1 2.0 1 $3.00 \times (NB. PIN + 1) + 0.65$ $B = 3.00 \times (NB. PIN + 1) + 0.65$ $B = 3.00 \times (NB. PIN + 1) + 0.65$ $B = 3.00 \times (NB. PIN + 1) + 0.65$				37 OPERATING TEM COMPLIANCE: LE ELECTRICAL CURRENT RATIN WORKING VOLTA INSULATOR RESI DIELECTRIC WIT CONTACT RESIST STANDARD N CERTIFIED: A SOLDERING	PERATURE: -40 UP TO 105 °C AD FREE AND ROHS GE: 250 VAC STANCE: >1000 MOHM HSTANDING VOLTAGE: 1500 VAC/MN FANCE: 10 mOHM MAX	В
F PROJECTION: GENERAL TOLERANCE E $x = \frac{+}{0.2}$ XX = $\frac{+}{0.15}$	4.10±0			TAPE AND REEL DIMENSION A = 3.00 × (NB. PII	N -1)	C
D D D C APPROVAL: BBu UNIT: MM DESCRIPTION: 3.00 MM SMT SINGLE ROW MALE VERTICAL HEADER WITH SCALE: SMT SOLDER TABS	F Image: C B Image: C	APPROVAL: BBu	.X = +/_ 0.2 .XX = +/_ 0.15 UNIT: MM SCALE:	SMT SOLDER TABS	MALE VERTICAL HEADER WITH	믿

	1	2		3	4	5		Г
		PULL OUT	DIRECTION	0.5		el ⁵ <u>2</u> Cover		A
								в
Rc	02-03 32 14.2 300 04-07 44 20.2 300 08-11 56 26.2 300 12 72 34.2 300 Note: 1.All dimensions meet 2.Material: BK Conduct 100% recycle 3.Thickness: 0.50±0.05 4.Carton Size:350*350*	7210051500412003900EIA-481-3 requirementive Polystyrene Alloyable.simm	ts.					С
F E D C B A REV	DATE FIL	E BY	APPROVAL: BBu	GENERAL TOLERANCE .X = ⁺ /_ 0.2 .XX = ⁺ /_ 0.15 UNIT: MM SCALE: SHEET: 2/3 DRAW: AK	WÜRTH ELEKTRONIK DESCRIPTION: 3.00 MM SMT SINGLE ROW I SMT SOLDER TABS WERI PART NO: 662 3xx 131 822	MALE VERTICAL HEADER WITH	SIZE	

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE	O		1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĪK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	D
В					SCALE:			Р
A	10-SEP-14	PDF	QL]	SHEET: 3/3	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			