	1		2		3	4	5	
	2	After cabling			efore cabling	TECHNICAL CHARAG MATERIAL INSULATOR: PBT FLAMMABILITY RATI COLOR: BLACK METAL: PHOSPHOR PLATING: TIN QUALITY CLASS: 25 ENVIRONMENTAL	NG: UL94V0 BRONZE MATING CYCLES RATURE: -40°C UP TO +125°C FREE AND ROHS 3 A : 50 VAC TAGE: 500 VAC/MIN ANCE: >1000 MΩ ICE: 20 mΩ MAX	
Ro	oHS Compliant		PROJECT	-10N: GE	A = (nb. pin- B = (nb. pin NERAL TOLERANCE ±0,1			
F E D	17-JUN-16	DESCRIPTION	AK					10
F E	17-JUN-16 07-DEC-15 20-OCT-15 19-SEP-14	DESCRIPTION MECHANICAL / PACK UPDATE PDF	AK APPROVA	SC	IT: MM ALE: EET: 1/2	DESCRIPTION: 2.54 MM AUTOCOM SINGI IDC RECEPTACLE FOR AWG#28-26 WITH SIDE WERI PART NO: 661 0xx 152 222		SIZE

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В					SCALE:			Γ
Α	10-SEP-14	PDF	QL		SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			