1	2	3	4	5	
	,3 ,3	Ø 1,3 0 0 0 0 0 0 0 0 0 0 0 0 0	2 COMPLIANCE: LEAD FRI ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTAGE: WITHSTANDING VOLTAGE: CONTACT RESISTANCE: PONENT VIEW STANDARD CERTIFIED: E15093 CERTIFIED: 400213	UL94V0 ER ALLOY / Ni+Sn EL / Zn ALLOY / Sn JRE: -30°C UP TO +120°C EE AND ROHS UL VDE 16A 24A 300VAC 750VAC EE: 1,6KV 3KV 20 mΩ MAX	,
		Ø 1 A = (nb. pin- B = (nb. pin-	STRANDED WIRE: 30- TORQUE: WIRE STRIPE LENGTH: 7 SCREW: M3 PITCH: 10 mm SOLDERING JEDEC LEAD FREE WAV PACKAGING		(
RoHS Compliant G F E D	PROJECTION:	GENERAL TOLERANCE			
C B B A A 25-AUG-14 REV DATE FILE	APPROVAL: QL AK BY	UNIT: MM SCALE: SHEET: 1/2 DRAW: AK	DESCRIPTION: SERIE 1368 - 10.00 MM - VERT PRESSURE CLAMP - GLOW WIRE PLASTIC - 1 WERI PART NO: 691 136 800 0xx	WR-TBL	^{SIZE} [A4

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В					SCALE:			Γ
A	10-SEP-14	PDF	QL		SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			