1	2	3	4	5		
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$			TECHNICAL CHARA MATERIAL I INSULATOR: PA6/66 FLAMMABILITY RAT COLOR: GREEN METAL HOUSING: C TERMINAL SCREW: WIRE GUARD: COPI WIRE GUARD: COPI S,81 7,62 ELECTRICAL CURRENT RATING:	CTERISTICS ING: UL94V0 OPPER ALLOY / Ni+Sn STEEL / Zn PER ALLOY / Ni+Sn RATURE: -30°C UP TO +120°C D FREE AND ROHS UL VDE 16A 24A E: 300VAC 750VAC LTAGE: 1,6KV 3KV NCE: 20 mΩ MAX 50931 CAT. N°: MRT5 (2)		В
RoHS Compliant G F E D C	PROJECTION:	m	Din-1) x pitch Din x pitch) WIRE STRIPE LENG SCREW: M3 PITCH: 7,62 mm SOLDERING JEDEC LEAD FREE PACKAGING BOX DESCRIPTION: SERIE 2534 - 7.62 MM - V	TH: 6 mm WAVE SOLDERING	SIZE	С
B A 22-JUN-15 PDF	AK APPROVAL: FBr	SCALE: SHEET: 1/2	RISING CAGE CLAMP - WR-TBL WERI PART NO: 691 253 400 0xx		A4	D
REV DATE FILE	BY	DRAW: AK				L

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	lD
В]	SCALE:			٢
A	10-SEP-14	PDF	QL	1	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			