1		2		3		4	5	
	2,5	3±0,3			£0,2	TECHNICAL CHARACTERIST MATERIAL INSULATOR: PC FLAMMABILITY RATING: ULS COLOR: GREY METAL HOUSING: COPPER ENVIRONMENTAL OPERATING TEMPERATURE COMPLIANCE: LEAD FREE A ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTAGE: CONTACT RESISTANCE: 20 STANDARD STANDARD CERTIFIED: E150931	TICS 94V0 ALLOY / Ni+Sn E: -30°C UP TO +120°C AND ROHS UL VDE 14A 16A 300VAC 250VAC 1,6KV 2,5KV mΩ MAX CAT. N°: CUM (2) TYPE: CUM	
				A = (nb. pin B = (nb. pin				
RoHS Compliant G F E D				GENERAL TOLERANCE ±0,1	WÜRTH ELEKT			
C B A 22-AUG-14 REV DATE	PDF FILE	AK BY	APPROVAL: QL	UNIT: MM SCALE: SHEET: 1/2 DRAW: AK	DESCRIPTION: S VERTICAL) - GLO WERI PART NO: 6	ERIE 3867 - 5.00 MM - PCB HEAI W WIRE PLASTIC - WR-TBL 591 386 700 0xx		SIZE A4

1	2	3	4	5	-
					_

А

В

С

## **Cautions and Warnings:**

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	RoHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F								
E								
D				1		WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В					SCALE:			٢
A	10-SEP-14	PDF	QL	]	SHEET: 2/2	WERI PART NO: DISCLAIMER	<b>A4</b>	
REV	DATE	FILE	BY		DRAW: QL			