typ. 0,9 typ.

2,8 ±0,2

1

¥////

Hatan

0,9 typ.


±0,2

2,8

2,8 ±0,2

Marking

Recommended Land Pattern: [mm]



Schematic:


DC Resistance P_{DC} @ 20 °C 796 mΩ Self Resonant Frequency f_{res} 15 MHz Certification: RoHS Approval Compliant [2011/65/EU&2015/863] REACh Approval Conform or declared [[EC]1907/2006] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] K recommended that the temperature of the component does not exceed +125 °C unde case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH Moisture Sensitivity Level (MSL) 1	DC Resistance	nDC	@ 20 °C	745	mΩ	ιyμ			
Certification: RoHS Approval Compliant [2011/65/EU&2015/863] REACh Approval Conform or declared [(EC)1907/2006] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to 1 _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	DC Resistance	R _{DC}	@ 20 °C	796	mΩ	ma			
RoHS Approval Compliant [2011/65/EU&2015/863] REACh Approval Conform or declared [(EC)1907/2006] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [JEDEC 1249-2-21] General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	Self Resonant Frequency	f _{res}		15	MHz	typ			
REACh Approval Conform or declared [(EC)1907/2006] Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	Certification:								
Halogen Free Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	RoHS Approval		Compliant [2	2011/65/EU&2015/8	863]				
Halogen Free Conform [IEC 61249-2-21] General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	REACh Approval		Conform or declared [(EC)1907/2006]						
General Properties: It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) Operating Temperature -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging)	Halogen Free		Conforn	n [JEDEC JS709B]					
It is recommended that the temperature of the component does not exceed +125 °C under case conditions Ambient Temperature (referring to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	1 Halogen Free		Conform	n [IEC 61249-2-21]					
to I _R) -40 up to +35 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH	General Properties:								
to I _R) -40 up to +85 °C Operating Temperature -40 up to +125 °C Storage Conditions (in original packaging) < 40 °C ; < 75 % RH		erature of t	ne component does	s not exceed +125 °	°C under	wor			
Storage Conditions (in original packaging)< 40 °C ; < 75 % RH	It is recommended that the temp	cas	e conditions		°C under	' wor			
packaging)	It is recommended that the temp Ambient Temperature (referrin	cas	e conditions		°C under	' wor			
Moisture Sensitivity Level (MSL)	It is recommended that the temp Ambient Temperature (referrin to I _R)	cas	e conditions -40) up to +85 °C	°C under	- wor			
	It is recommended that the temp Ambient Temperature (referrin to I _R) Operating Temperature Storage Conditions (in original	g	-40) up to +85 °C up to +125 °C	°C under	- wor			
Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently	It is recommended that the temp Ambient Temperature (referrin to I _R) Operating Temperature Storage Conditions (in original	g	-40) up to +85 °C up to +125 °C °C ; < 75 % RH	°C under	r wor			
	It is recommended that the temp Ambient Temperature (referrin to I _R) Operating Temperature Storage Conditions (in original packaging) Moisture Sensitivity Level (MS	g I L)	-40 -40 < 40) up to +85 °C up to +125 °C °C ; < 75 % RH 1		- w(
CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE PROJECTION METHOD	It is recommended that the temp Ambient Temperature (referrin to I _R) Operating Temperature Storage Conditions (in original packaging) Moisture Sensitivity Level (MS Test conditions of Electric	Cas g l L) al Propertie	e conditions -40 -40 < 40 s: +20 °C, 33 % R) up to +85 °C up to +125 °C °C ; < 75 % RH 1 H if not specified dit					
CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE PROJECTION METHOD CO2.003 2020-06-09 DIN ISO 2768-1m	It is recommended that the temp Ambient Temperature (referrin to I _R) Operating Temperature Storage Conditions (in original packaging) Moisture Sensitivity Level (MS Test conditions of Electric	Cas g l L) al Propertie	e conditions -40 -40 < 40 s: +20 °C, 33 % R) up to +85 °C up to +125 °C °C ; < 75 % RH 1 H if not specified dit					

Electrical Properties:

Properties		Test conditions	Value	Unit	Tol.
Inductance	L	100 kHz/ 1 mA	27	μH	±20%
Rated Current	I _R	$\Delta T = 40 \text{ K}$	0.45	A	typ.
Saturation Current	I _{SAT}	IΔL/LI < 35 %	0.67	A	typ.
DC Resistance	R _{DC}	@ 20 °C	745	mΩ	typ.
DC Resistance	R _{DC}	@ 20 °C	796	mΩ	max.
Self Resonant Frequency	f _{res}		15	MHz	typ.

Scale - 5:1 **Product Marking:** Marking Ν F \bigcirc RoHS COMPLIANT HALOGEN REACh COMPLIANT Würth Elektronik eiSos GmbH & Co. KG Inductor ORDER CODE EMC & Inductive Solutions WÜRTH Max-Eyth-Str. 1 744025270 74638 Waldenburg ELEKTRONIK Germany MORE THAN YOU EXPECT Tel. +49 (0) 79 42 945 - 0 www.we-online.com SIZE/TYPE BUSINESS UNIT STATUS PAGE 1/6 2828 eiSos Valid eiSos@we-online.com


This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed or every electronic component which is used in electral crucits the reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in electrical crucits the reasonably expected to cause severe personal injury or death, public information network etc... Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in electrical crucits the reasonable value and realiability functions or performance.

Packaging Specification - Tape and Reel: [mm]

Packaging Specification - Reel: [mm]



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed or every electronic component which is used in electrical circuits that require high standard in eliability standard and reliability evaluation (automotive control, train control, ship control), train control, ship control, train control, tra

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

Profile Feature		Value
Preheat Temperature Min	T _{s min}	150 °C
Preheat Temperature Max	T _{s max}	200 °C
Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$	t _s	60 - 120 seconds
Ramp-up Rate (T _L to T _P)		3 °C/ second max.
Liquidous Temperature	Τ _L	217 °C
Time \mathbf{t}_{L} maintained above \mathbf{T}_{L}	tL	60 - 150 seconds
Peak package body temperature	Т _р	$T_p \leq T_c$, see Table below
Time within 5°C of actual peak temperature	t p	20-30 seconds, except Tp 260°C at tp 10 seconds
Ramp-down Rate (T _P to T _L)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature (T_c):

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly I Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

63 0	\mathfrak{G}		CHECKED	REVISION 002.003	DATE (YYYY-MM+DD) 2020-06-09	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	$- \bigcirc ($	€-
RoHS REACH COMPLIANT COMPLIANT	HALOGEN FREE				Shielded Ti	iny Power				
L/F	Würth Elektronik eßos Grahb & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany		Induct	or			ORDER CODE	025270		
	MORE THAN YOU EXPECT	einnany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE 2828			BUSINESS UNIT eiSos	status Valid		1	page 4/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-TPC ofWürth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the part, resulting in avoid of the warranty.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
 insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- · Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

B			CHECKED	REVISION 002.003	DATE (YYYY-MM+DD) 2020-06-09	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	$- \bigcirc \bigcirc$	€-
ROHS REACH COMPLIANT COMPLIANT	HALOGEN FREE	Würth Elektronik eiSos GmbH & Co. KG			Shielded Ti	iny Power				
	WURTH ELEKTRONIK	Wulur Dekalanik elsas anan a co. Ka EMC& Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Induct	or			ORDER CODE	025270)	
	MORE THAN YOU EXPECT	einany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 2828			BUSINESS UNIT eiSos	status Valid			page 5/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, ship control, train control, tra

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

63 0			CHECKED LISt	REVISION 002.003	DATE (YYYY-MM-DD) 2020-06-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	3¢	€-
RoHS REACH COMPLIANT COMPLIANT	HALOGEN FREE		DESCRIPTION	C SMT S	Shielded T	iny Power				
L/F	WURTH ELEKTRONIK	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Induct	or		_	ORDER CODE	025270		
	MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 2828			BUSINESS UNIT eiSos	status Valid			^{AGE}

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in entential tracium signal, advantine, transportation (automotive control, train control, ship control), train control, ship control, train control, train control, train control, ship control, train control, ship control, train control, trai