1	2	3	4	5	
	A		COMPLIANCE: LEAD FI ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTA CONTACT RESISTANCI STANDARD STANDARD PITCH: 3.81 MM SOLDERING	S: UL94-V0 COPPER ALLOY N PED M2.5 TURE: -40 UP TO 115°C REE AND ROHS CULUS 8A 300VAC AGE: 1.6KV E: 20 mOhm max 414 AVE SOLDERING PROCESS	
RoHS Compliant G F E	PROJECTION:	GENERAL TOLERANCE .X = +/_ 0.2 .XX = +/_ 0.15			
D C B A 11-JUN-15 PDF REV DATE FILE	APPROVAL: FBr	UNIT: MM SCALE: SHEET: 1/2 DRAW: AK	DESCRIPTION: SERIE 3083 - 3.81 MM REVER FLANGES WERI PART NO: 691 308 330 0xx		SIZE

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	lD
В]	SCALE:			٢
A	10-SEP-14	PDF	QL	1	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			