1	2	3	4	5	
0 2 1 1.00 15.24±0.2 3.8	DIM L 2.54	mi 3.5 DIM B fill gi 2.54 fill gi gi fill	OMPLIANCE: LEAD Ø1.60 ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOL CONTACT RESISTAN STANDARD STANDARD STANDARD MECHANICAL PITCH: 5.08mm SOLDERING	NG: UL94-V0 S (CuZn) R TAIL PLATING: TIN RATURE: -40 UP TO 105°C FREE AND ROHS UL 15A : 300VAC TAGE: 1.6KV CE: 20 mOhm MAX	Ē
RoHS Compliant G F E D	LEE PROJECTION:		$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	20222426 2.80 57.88 62.96 68.04 5.72 50.80 55.88 60.96 ± 0.25 ± 0.25 44 46 48 13.76 118.84 123.92 26.68 111.76 116.84 ± 0.35 55.88 55.88	
		UNIT: MM	DESCRIPTION: SERIE 3365 - 5.08MM DOUB	LE LEVEL VERTICALE MALE	SIZE
C B 07-JUL-15 UPDATE	APPROVAL: FBr	SCALE:	PCB HEADER WITH FLANGES TYPE WR-TE		^{312L} [

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	lD
В]	SCALE:			٢
A	10-SEP-14	PDF	QL	1	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			