**Dimensions:** [mm]

#### Properties **Test conditions** Value Unit Inductance 1 MHz/ 10 mA 2.2 μH L **Rated Current** $\Delta T = 40 \text{ K}$ 1.75 $I_R$ Saturation Current $|\Delta L/L| < 30 \%$ 3.35 ISAT А q R<sub>DC</sub> @ 20 °C 90 **DC Resistance** mΩ G R<sub>DC</sub> **DC Resistance** @ 20 °C 108 mΩ N ω N Peak Voltage $V_{P}$ 25 f<sub>res</sub> 46 Self Resonant Frequency MHz 0,75 ±0,2 **Certification:** 3.0 ±0.2 0,85 1,5 **RoHS Approval** Compliant [2011/65/EU&2015/863] **REACh Approval** Conform or declared [(EC)1907/2006] Scale - 10:1 **Halogen Free** Conform [JEDEC JS709B] 2,7 ±0,2 Halogen Free Conform [IEC 61249-2-21] Schematic: 1,2 max. **General Information:** It is recommended that the temperature of the component does not exceed +125 °C under worst case conditions **Ambient Temperature (referring** -40 up to +85 °C to I<sub>R</sub>) 2 ą **Operating Temperature** -40 up to +125 °C 0 ĉ Storage Conditions (in original < -40 °C; < 75 % RH packaging) Moisture Sensitivity Level (MSL) Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Scale - 10:1 **Product Marking:** Start of Winding . CHECKED REVISION GENERAL TOLERANCE PROJECTION METHOD DATE (YYYY-MM-DD) GЭ ChriB 001.001 2019-11-18 DIN ISO 2768-1m DESCRIPTION RoHS REACh COMPLIANT HALOGEN **WE-LQSH SMT Semi-Shielded High** Würth Elektronik eiSos GmbH & Co. KG **Saturation Power Inductor** ORDER CODE EMC & Inductive Solutions WÜRTH Max-Eyth-Str. 1 74405031022 74638 Waldenburg ELEKTRONIK Germany MORE THAN SIZE/TYPE Tel. +49 (0) 79 42 945 - 0 BUSINESS UNIT STATUS YOU EXPECT www.we-online.com 3012 Valid eiSos eiSos@we-online.com

This electronic component has been designed and developed for usage in general electronic equipment only. This product is neasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, train control, tr

## **Recommended Land Pattern: [mm]**

**Electrical Properties:** 

Tol.

±20%

max.

typ.

typ.

max.

max.


typ.

PAGE

1/7


А

V



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in effectival crustel severation (automotive control, train control, ship control), train control, ship control, train control, ship cont

## Packaging Specification - Tape and Reel: [mm]



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in effectival crustel severation (automotive control, train control, ship control), train control, ship control, train control, ship cont

Vicmu         Vicmu	No. of Reel (pcs.)	Material	Vp.         Vp. <th>lo. of nner Carton (pcs.)</th> <th>Oty. C Naterial 80000 Paper</th> <th></th>	lo. of nner Carton (pcs.)	Oty. C Naterial 80000 Paper	
byp. byp. byp. 180,00 120,00 180,00	10 20000	Paper	CHECKED REWISION DATE (YYYY-MM-DD)	GENERAL TOLERANCE		
		Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg	ChriB 001.001 2019-11-18 UESCRIPTION WE-LQSH SMT Semi-Shi Saturation Power Induct		ORDER CODE 74405031022	Ψ
c component has been designed and developed for usage in general electronic equipment only. This product is not authorized for u	WURTH ELEKTRONIK MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SZEJTYPE 3012	BUSINESS UNIT eiSos	status Valid	PAGE 4/7

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety restriction. Quipment of were leactrical cruited because severe personal injury or death, unless the parties have executed an agreement specifically governing such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in the require injury and reliability evaluation checks for safety must be performed on every electronic component which is used in the require injury and reliability evaluation checks for safety must be performed on every electronic component which is used in the require injury and reliability evaluation checks for safety must be performed on every electronic component which is used in the relatival injury of eath in the electrical cruited because the expected on every electronic component which is used in the relatival injury of eath in the electrical cruited because the electrical cruited b

## **Classification Reflow Profile for SMT components:**



## **Classification Reflow Soldering Profile:**

Profile Feature		Value
Preheat Temperature Min	T <sub>s min</sub>	150 °C
Preheat Temperature Max	T <sub>s max</sub>	200 °C
Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$	t <sub>s</sub>	60 - 120 seconds
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )		3 °C/ second max.
Liquidous Temperature	TL	217 °C
Time $t_L$ maintained above $T_L$	tL	60 - 150 seconds
Peak package body temperature	Т <sub>р</sub>	$T_p \le T_c$ , see Table below
Time within 5°C of actual peak temperature	t p	20 - 30 seconds
Ramp-down Rate (T <sub>P</sub> to T <sub>L</sub> )		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

## Package Classification Reflow Temperature (T<sub>c</sub>):

Properties	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000		
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C		
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C		
PB-Free Assembly I Package Thickness > 2.5 mm	250 °C	245 °C	245 °C		

refer to IPC/ JEDEC J-STD-020E

	Rest COMPLIANT       REACH COMPLIANT       REACH READ HALOGEN         WURTH ELEKTRONIK       Würth Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Company		CHECKED	REVISION 001.001	DATE (YYYY-MM-DD) 2019-11-18	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	$- \bigcirc ($	€-	
					Semi-Shiel	-					
			EMC & Inductive Solutions Max-Eyth-Str. 1	Saturation Power Inducto			r	ORDER CODE 74405031022			
	MO	RE THAN J EXPECT	elinary (n) 79 42 945 - 0 www.we-online.com elSos@we-online.com	size/type 3012			BUSINESS UNIT eiSos	status Valid			page 5/7

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

## **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of WE-LQSH of Würth Elektronik eiSos GmbH & Co. KG:

#### **General:**

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be were used within the datasheet specified values. If the usage and operation
  conditions specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, as the core may flake apart.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

#### **Product specific:**

#### Soldering:

- · The solder profile must comply with the Würth Elektronik technical soldering specification. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the part, resulting in avoid of the warranty.

#### **Cleaning and Washing:**

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
  insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

#### Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the core or wire contacts. We
recommend a manual inspection after potting to avoid these effects.

#### **Storage Conditions:**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- · Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.

#### Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

Revis       REACH       HALDGEH         COMPLANT       REACH       HALDGEH         WURTH       REACH       HALDGEH         WURTH       REACH       REACH         RAW       RAW       RAW         RAW       RAW       Reach         Reach       Reach       Reach		CHECKED ChriB	REVISION 001.001	DATE (YYYY-MM-DD) 2019-11-18	GENERAL TOLERANCE DIN ISO 2768-1 m	PROJECTION METHOD		€-
				Semi-Shie				
		Satura	tion Pow	ver Inducto	r	ORDER CODE 7440503	1022	
MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE 3012			BUSINESS UNIT eiSos	status Valid	1	PAGE 6/7

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in ententiability availation (submitive control, ship control), train control, ship control, stansportation signal, disaster prevention, medical, public information network etc... Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electrical circuits that require high stately and reliability availations or performance.

### **Important Notes**

## The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

#### **1. General Customer Responsibility**

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

#### 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

### 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

	Wirth Elektronik elSos GmbH & Co. KG         Würth Hektronik elSos GmbH & Co. KG         BUCK         Max-Eyth-Str. 1         74638 Walderburg		CHECKED ChriB	REVISION 001.001	DATE (YYYY-MM-DD) 2019-11-18	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	$\exists$	€-	
			WE-LQSH SMT Semi-Shielded High					· · · · · · · · · · · · · · · · · · ·			
			Satura	tion Pow	ver Inducto	r	ORDER CODE	)5031022			
	./-	MORE THAN         Germany           YOU EXPECT         Tel. +49 (0) 79 42 945 - 0           www.we-online.com         elSos@we-online.com	Tel. +49 (0) 79 42 945 - 0 www.we-online.com	SIZE/TYPE 3012			BUSINESS UNIT eiSos	status Valid		- 1	PAGE 7/7

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed or every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, train control, ship contr