




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




TERM. NO.'s FOR REF. ONLY



6D Customer to tie terminals 6+7 and 9+10 on PC board.

Application of the transformer allows for the leadwires between terminals 6&7 and 9&10 to solder bridge.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6C D.C. RESISTANCE	3-5 @20°C	0.13 ohms ±15%
6C D.C. RESISTANCE	7-9 tie(6+7, 9+10) @20°C	0.006 ohms max.
INDUCTANCE	3-5 10kHz, 100mVAC, Ls	40.0uH ±10%
SATURATION CURRENT	3-5 20% rolloff from initial	3.2A
LEAKAGE INDUCTANCE	3-5 tie(7+9), 100kHz, 100mVAC, Ls	1uH typ., 2uH max.
DIELECTRIC	3-7 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-5):(6-9), tie(6+7, 9+10)	8:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Functional insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

6C Qualified to AEC-Q200.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6D	9/20	Method: Tape & Reel		Angles: ±1°	TRANSFORMER	750315835
6C	1/18	PKG-0499	Fractions: ±1/64	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
6B	10/16	www.we-online.com/midcom	Decimals: ±.005 [.13]			SPECIFICATION SHEET 1 OF 1
6A	6/16	SEE REVISION SHEET FOR REVISION LEVEL	Footprint: ±.005 [.13]			