




Dimensions: [mm]













Scale - 1:1

B

RoHS COMPLIANT







Electrical Properties:

Properties		Test conditions	Value	Unit	Tol.
Inductance	L	N1+N2/ 10 kHz/ 100 mV	1500	μH	±10%
Turns Ratio	n	N1+N2 : N3 : N4	4.5:1:0.5		
Saturation Current	I _{SAT}	N1+N2/ $ \Delta L/L < 20 \%$	0.65	A	typ.
DC Resistance 1	R _{DC 1}	N1+N2/20 °C	2.9	Ω	±10%
DC Resistance 2	R _{DC 2}	N3/ 20 °C	0.21	Ω	±10%
DC Resistance 3	R _{DC 3}	N4/ 20 °C	1.22	Ω	±10%
Leakage Inductance	L _S	N1+N2/ 100 kHz/ 100 mV	35	μH	max.
Insulation Test Voltage	V _T	N1,2,4 => N3	4500	V (AC)	
Insulation Test Voltage	V _{T2}	N1,2 => N4	1000	V (AC)	

Certification:

CHECKED

DESCRIPTION

SIZE/TYPE

EE16/8/5

IKK

REVISION

007.001

LT3575/ LT3748

WE-FB Flyback Transformer suitable for LT3573/ LT3574/

DATE (YYYY-MM-DD)

2023-07-11

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACh Approval Conform or declared [(EC)19 General Information: Operating Temperature -40 °C up to +125 ° Storage Conditions (in original packaging) < 40 °C ; < 75 % I	
EACh Approval Conform or declared [(EC)1907/2006] eneral Information: -40 °C up to +125 °C orage Conditions (in original ackaging) < 40 °C ; < 75 % rH storage Conditions (for single arts) -20 °C up to +60 °C	
eneral Information:	
Operating Temperature	-40 °C up to +125 °C
	< 40 °C ;< 75 % rH
packaging)	
	-20 °C up to +60 °C
Acieture Consitivity Lovel (MSL)	1
NOISIULE SELISIUVILY LEVEL (INISL)	

GENERAL TOLERANCE

ISO 2768-1m

BUSINESS UNIT

Midcom

PROJECTION METHOD

ORDER CODE

STATUS

Valid

750811048

 \oplus

PAGE

1/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electricial circuits that reliability and reliability functions or performance.

WÜRTH

ELEKTRONIK

MORE THAN YOU EXPECT 121 Airport Drive

United States

57201 Watertown, SD

Phone: +1 (605) 886-4385

midcom@we-online.com

www.we-online.com/midcom

Typical Application:

Properties		Value	Unit
Input Voltage	V _{in}	120 - 375	V (DC)
Switching Frequency	f _{switch}	300	kHz
Output Voltage 1	V _{Out1}	30	V
Output Current 1	I _{Out1}	0.3	Α
Auxiliary Voltage	Vaux	15	V


Input: N1 + N2 Output 1: N3 Auxiliary: N4 Table shows a typical flyback application. Values may vary by application.


Designed to Comply With:

Standard	Condition
IEC61558-2-17	Reinforced insulation for a primary circuit at a working voltage of 400VDC.

	Reference in the second			CHECKED	revision 007.001						
				WE-FB Flyback Transformer suitable for LT3573/ LT3574/				ORDER CODE			
	WURTH ELEKTRON MORE THA	KTRONIK United States		/ LT374		/	750	811048			
	MORE THA YOU EXPEC		605) 886-4385 ine.com/midcom e-online.com	SIZE/TYPE EE16/8/5			BUSINESS UNIT Midcom	status Valid		- 1	page 2/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the runterioa circuits that must control such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus that must and require high safety and reliability an





				REVISION 007.001	DATE (YYYY-MM-DD) 2023-07-11	GENERAL TOLERANCE				
Roh5 PEACh COMPLIANT COMPLIANT		WE-FB Flyback Transformer								
		Wurth Electronics Midcom Inc. Headquarters 121 Airport Drive 57201 Watertown, SD United States		e for LT3 5/ LT3748	3573/ LT35 8	74/	ORDER CODE	811048		
	MORE THAN YOU EXPECT	Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com	SIZE/TYPE EE16/8/5			BUSINESS UNIT Midcom	status Valid		PAGE 3/8	

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus are neither equire high safety and reliability transportation signal, disaster prevention, medical, public information network etc... Würth Elektronik eiSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic equipment advice and evaluation checks for safety must be performed on every electronic component which is used in electronic equipments advice and evaluation checks for safety must be performed on every electronic component which is used in electronic equipments advice and evaluation checks for safety must be performed on every electronic component which is used in electronic equipment advice and evaluation checks for safety must be performed on every electronic component which is used in electronic equipment advice and evaluation is every electronic equipment advice ad

L _c (mm)W _c (mm)H _c (mm)No. of Tray (pcs.)Qty. (pcs.)MaterialTolerance±5.0±5.0±5.0Value330,20330,20212,738560kraft corrugated, B-C flute.						
Wurth Electronics Michael In Headquarters CIL	PTION E-FB iitable	Flybac 6 for L1 6 LT374	Date (YYYYMM-DD) 2023-07-11 k Transforn 73573/ LT35 18	GENERAL TOLERANCE ISO 2768-1m	ORDER CODE 7508	PROLECTION METHOD
WÜRTH 121 Arport Drive 121 Arport Drive LT3 ELEKTRONIK 57201 Watertown, SD LT3 MORE THAN Phone: +1 (605) 886-4385 SZE/TM YOU EXPECT www.we-online.com/midcom SZE/TM	YPE			BUSINESS UNIT Midcom	status Valid	_

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the runterioa circuits that must control such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus that must and require high safety and reliability an

-Φ;

PAGE

4/8

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

Profile Feature		Value
Preheat Temperature Min	T _{s min}	150 °C
Preheat Temperature Max	T _{s max}	200 °C
Preheat Time t_s from $T_{s \min}$ to $T_{s \max}$	t _s	60 - 120 seconds
Ramp-up Rate (T _L to T _P)		3 °C/ second max.
Liquidous Temperature	TL	217 °C
Time \mathbf{t}_{L} maintained above \mathbf{T}_{L}	tL	60 - 150 seconds
Peak package body temperature	Т _р	$T_p \le T_c$, see Table below
Time within 5°C of actual peak temperature	t _p	20 - 30 seconds
Ramp-down Rate (T _P to T _L)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature (T_c):

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000		
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C		
PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C		
PB-Free Assembly I Package Thickness > 2.5 mm	250 °C	245 °C	245 °C		

refer to IPC/ JEDEC J-STD-020E

63	Rohs COMPLIANT COMPLIANT		CHECKED							
RoHS REACI			WE-FB Flyback Transformer suitable for LT3573/ LT3574/							
I-//5	WURTH ELEKTRONIK	Wurth Electronics Midcom Inc. Headquarters 121 Airport Drive 57201 Watertown, SD United States		e for LT: 5/ LT374		74/	ORDER CODE	811048	3	
./-	MORE THAN YOU EXPECT	Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com	SIZE/TYPE EE16/8/5			BUSINESS UNIT Midcom	status Valid			page 5/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Furth	er information	REDEXPERT:
Comp	onent Libraries:	Calculate losses for
	Altium_WE-FB (23a)	
e 193	Downloads_CADENCE_WE-FB (22a)	
e 193	Download_Cadstar_WE-FB (19a)	
EXG	Eagle_WE-FB (19a)	
231	Download_IGS_750811048	
REP	PSpice_WE-FB (22b)	
ap	Download_STP_750811048	
Free S	Sample Order:	
Order fr	ee samples of this article directly here!	

Tutorials:

Overview-Power Magnetics (PDF)

				CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLEPANCE IKK 007.001 2023-07-11 ISO 2768-1m								
	RTH	Wurth Electronics Midcom Inc. Headquarters 121 Airport Drive 57201 Watertown, SD United States	suitabl	-	Transform 3573/ LT35 8		ORDER CODE 7508	811048	}			
MOI	RE THAN J EXPECT	Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com	SIZE/TYPE EE16/8/5			BUSINESS UNIT Midcom	status Valid		1	PAGE 6/8		

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation signal, disaster prevention, medical, public information network etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Calculate losses for 750811048 in REDEXPERT

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-FB of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, as the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the component, resulting in avoid of the warranty.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
 insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- · Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- Due to heavy weight of the components, strong forces and high accelerations may have the effect to damage the electrical connection
 or to harm the circuit board and will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

Rends Rends COMPLIANT REACH REACH REAC		CHECKED				PROJECTION METHOD			-
		suitab	WE-FB Flyback Transformer suitable for LT3573/ LT3574/ LT3575/ LT3748				ORDER CODE 750811048		
MORE THAN YOU EXPECT	Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com	SIZE/TYPE EE16/8/5			BUSINESS UNIT Midcom	status Valid		1	PAGE 7/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

	Rots COMPLANT COMPLANT		CHECKED	REVISION 007.001	DATE (YYYY-MM-DD) 2023-07-11	general tolerance ISO 2768-1m		PROJECTION METHOD		€-
				WE-FB Flyback Transformer						
k/ 2		Wurth Electronics Midcom Inc. Headquarters 121 Airport Drive 57201 Watertown, SD United States		suitable for LT3573/ LT3574/ LT3575/ LT3748				ORDER CODE 750811048		
	YOLLEXPECT www.we-online.com/mid	Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com	COM SIZE/TIPE			BUSINESS UNIT Midcom	status Valid		- 1	PAGE 8/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.