



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





TERM. NO.'s FOR REF. ONLY



DOT LOCATES TERM. #1

LOT CODE & DATE CODE



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-5 @20°C	1.172 ohms ±10%
D.C. RESISTANCE	10-6 @20°C	24.17 ohms ±10%
INDUCTANCE	1-5 10kHz, 100mVAC, Ls	1.00mH ±10%
INDUCTANCE	10-6 10kHz, 100mVAC, Ls	15.00mH ±10%
LEAKAGE INDUCTANCE	1-5 tie(10+8+6), 10kHz, 100mVAC, Ls	6.31uH typ., 7.50uH max.
DIELECTRIC	1-10 500VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(10-6):(1-5)	3.845:1, ±1%

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-0499 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1°      Decimals: ±.005 [.13] Fractions: ±1/64      Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750311549</b>
6A	12/10	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311549	SPECIFICATION SHEET 1 OF 1