Turns Ratio N1 : N2 : N3 : N4 : N5 4.17:1:1:0.25:0.58 n 28.5 Saturation Current N1/ $|\Delta L/L| < 20 \%$ 2 ISAT 6 R_{DC} N1/20 °C 0.615 DC Resistance 1 12-R_{DC} **DC Resistance 2** N2/ 20 °C 0.052 R_{DC} **DC Resistance 3** N3/ 20 °C 0.052 R_{DC} **DC Resistance 4** N4/ 20 °C 0.113 **DC Resistance 5** R_{DC} N5/ 20 °C 0.254 N1/ 100 kHz/ 100 mV Leakage Inductance LS 4.2 3.81 V_{T} **Insulation Test Voltage** N1,4,5 => N2,3 4500 ø1,32 26,3 max. - V_{T_2} N1 => N4,5 **Insulation Test Voltage** 500 SCALE 1:1 **Certification:** 14,48 max. Schematic: **RoHS Approval** Compliant [2011/65/EU&2015/863] - 3/5 **REACh Approval** Conform or declared [(EC)1907/2006] 3 0,6 sq. N1 **General Information:** . **Operating Temperature** -40 up to +125 °C N2 33 max. Storage Conditions (in original < 40 °C; < 75 % RH packaging) 10 N4 **Storage Conditions (for single** (-20 up to +60 °C ₩E parts) Markina N3 Moisture Sensitivity Level (MSL) 1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently 11 N5 SCALE 1:1 **Product Marking:** Pin 1 . CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE PROJECTION METHOD 750811645 F EOI 003.001 2023-03-29 ISO 2768-1m Marking Lot and date code DESCRIPTION RoHS COMPLIANT REACh COMPLIANT **WE-OLEFD Offline Flyback** Transformer Wurth Electronics Midcom Inc. Headquarters ORDER CODE 121 Airport Drive WÜRTH 750811645 57201 Watertown, SD **ELEKTRONIK** United States MORE THAN Phone: +1 (605) 886-4385 SIZE/TYPE BUSINESS UNIT STATUS www.we-online.com/midcom

This electronic component has been designed and developed for usage in general electronic equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eißos GmbH Co KG products are neither designed nor intended for use in rarsportation, submarine, transportation, transported transportation, transportation, transportation, transportati

midcom@we-online.com

EFD25

YOU EXPECT

Recommended Land Pattern: [mm]

Electrical Properties:

Test conditions

N1/ 10 kHz/ 100 mV

Midcom

Valid

Value

470

Unit

μН

А

Ω

Ω

Ω

Ω

0

μH

V (AC)

V (AC)

Tol.

±10%

typ.

±10%

±20%

±20%

±10%

±10%

max.

PAGE

1/7

Properties

Inductance

Typical Application:

| Properties | | Value | Unit |
|---------------------|---------------------|----------|--------|
| Input Voltage | V _{in} | 85 - 265 | V (AC) |
| Switching Frequency | f _{switch} | 68 - 100 | kHz |
| Output Voltage 1 | V _{Out1} | 24 | V |
| Output Current 1 | I _{Out1} | 710 | mA |
| Output Voltage 2 | V _{Out2} | 24 | V |
| Output Current 2 | I _{Out2} | 710 | mA |
| Auxiliary Voltage | V _{aux} | 20 | V |
| Auxiliary Voltage 1 | V _{aux 1} | 6 | V |
| Auxiliary Voltage 2 | V _{aux 2} | 14 | V |

Input: N1 Output 1: N2 Output 2: N3 Auxiliary: N4+N5 Auxiliary 1: N4

Auxiliary 2: N5


Table shows a typical flyback application. Values may vary by application.

Designed To Comply With:

| Standard | Condition |
|---------------|---|
| IEC61558-2-16 | Reinforced insulation for a primary circuit at a working voltage of 400VDC. |

| Rolfs REACN | | CHECKED REVISION DATE (YYYYMM-DD) GENERAL TOLERANCE EOI 003.001 2023-03-29 ISO 2768-1m DESCRIPTION EXEMPTION EXEMPTION EXEMPTION | | | | | PROJECTION METHOD | | €- |
|--|------------------------------------|--|--|--|-------------------------|-------------------------|----------------------|---|-------------|
| WURTH Electronics Midcom Inc. Headqu. 121 Airport Drive 57201 Watertown, SD United States | | WE-OLEFD Offline Flyback Transformer | | | | ORDER CODE 750811645 | | | |
| MORE THAN YOU EXPECT | MORE THAN Phone: +1 (605) 886-4385 | | | | BUSINESS UNIT Midcom | status Valid | | 1 | PAGE 2/7 |

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the runterioa circuits that must control such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus that must and require high safety and reliability an



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electricial circuits that reliability and reliability functions or performance.

| waging specification - carton, fining | | | | | | |
|---|---|---|---------------|----------------------------------|--|-------------|
| L _C (mm) W _C (mm) H _C (mm) Tolerance ±5,0 ±5,0 ±5,0 Value 330,20 330,20 212,73 | No. of Uty. (pcs.) Material 7 294 kraft corrugated, B-C flute. | | | | | |
| | ROHS COMPLANT REACH COMPLANT | CHECKED REVISION EOI 003.00 DESCRIPTION WE-OLEFD | 0ffline Flyba | GENERAL TOLERANCE ISO 2768-1m | PPOLECTION METHOD | |
| | WÜRTH ELEKTRONIK MORE THAN YOU EXPECT Wurth Electronics Midcom Inc. Headquarters 121 Arport Drive 57201 Watertown, SD United States Wow.we-online.com/midcom midcom@we-online.com | | er | BUSINESS UNIT Midcom | order code 750811645 status Valid | РАGЕ 4/7 |

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation, transportation, transportation, medical, public information network etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Classification Wave Soldering Profile:



---- max temperature procedure

Classification Wave Soldering Profile:

| Profile Feature | | Pb-Free Assembly | Sn-Pb Assembly | | | |
|--|--------------------|---|---|--|--|--|
| Preheat Temperature Min | T _{s min} | 100 °C | 100 °C | | | |
| Preheat Temperature Typical T _{s typic} | | 120 °C | 120 °C | | | |
| Preheat Temperature Max | T _{s max} | 130 °C | 130 °C | | | |
| Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$ | t _s | 70 seconds | 70 seconds | | | |
| Ramp-up Rate ΔT | | 150 °C max. | 150 °C max. | | | |
| Peak Temperature | Т _р | 250 °C - 260 °C | 235 °C - 260 °C | | | |
| Time of actual peak temperature | tp | max. 10 seconds max. 5 seconds each wave | max. 10 seconds max. 5 seconds each wave | | | |
| Ramp-down Rate, Min | | ~ 2 K/ second | ~ 2 K/ second | | | |
| Ramp-down Rate, Typical | | ~ 3.5 K/ second | ~ 3.5 K/ second | | | |
| Ramp-down Rate, Max | | ~ 5 K/ second | ~ 5 K/ second | | | |
| Time 25 °C to 25 °C | | 4 minutes | 4 minutes | | | |

refer to EN61760-1:2006

| | 63 🕖 | | | CHECKED EOI | REVISION 003.001 | DATE (YYYY-MM-DD) 2023-03-29 | general tolerance ISO 2768-1m | | PROJECTION METHOD - | | €- |
|--|--|--|---|----------------|---------------------|---------------------------------|----------------------------------|-------------------------|------------------------|-------------|----|
| | ROHS COMPLIANT REACH COMPLIANT WURTH ELEKTRONIK MODE THAN Wurth Electronics Midcom Inc. Headquarters 121 Airport Drive 57201 Watertown, SD United States | | WE-OLEFD Offline Flyback | | | | | - | | | |
| | | | 121 Airport Drive 57201 Watertown, SD United States | Transformer | | | | ORDER CODE 750811645 | | | |
| | ./- | MORE THAN Phone: -11 (605) 886-4385 YOU EXPECT www.we-online.com/midcom midcom@we-online.com | SIZE/TYPE EFD25 | | | BUSINESS UNIT Midcom | status Valid | | - 1 | page 5/7 | |

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the runterioa circuits that must control such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus that must and require high safety and reliability an

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-OLEFD of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, as the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the component, resulting in avoid of the warranty.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
 insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- Due to heavy weight of the components, strong forces and high accelerations may have the effect to damage the electrical connection
 or to harm the circuit board and will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

| Rohs REACH | | OFEORED REVISION DATE (YYY+MM-00) GENERAL TOLEPANOE EOI 003.001 2023-03-29 ISO 2768-1m DESCRIPTION | | | | | PROJECTION METHOD |] ⊕- |
|--|--------------------------|--|--|--|----|--------------------------------|----------------------|-------------|
| Wurth Electronics Midcom Inc. Headquarters 121 Aiport Drive 57201 Watertown, SD United States | | WE-OLEFD Offline Flyback Transformer | | | ck | ORDER CODE 750811645 | | |
| MORE THAN | Phone: +1 (605) 886-4385 | | | | | | | |

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

| | | CHECKED | REVISION 003.001 | DATE (YYYY-MM-DD) 2023-03-29 | general tolerance ISO 2768-1m | | PROJECTION METHOD | | €- | | |
|--|---|-------------------------|--|---------------------------------|----------------------------------|--|-------------------------|-----------------|-------------------------|--|-------------|
| | Rehts COMPLIANT REACH COMPLIANT WURTH ELEKTRONIK ELEKTRONIK United States United States | | WE-OLEFD Offline Flyback | | | | | | | | |
| | | | 121 Airport Drive 57201 Watertown, SD United States | Transformer | | | | | ORDER CODE 750811645 | | |
| | | MORE THAN YOU EXPECT | Phone: +1 (605) 886-4385 www.we-online.com/midcom midcom@we-online.com | SIZE/TYPE EFD25 | | | BUSINESS UNIT Midcom | status Valid | | | page 7/7 |

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.