

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:




PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	5.40 ohms max.
D.C. RESISTANCE	4-5 @20°C	1.20 ohms max.
D.C. RESISTANCE	7-9 @20°C	0.048 ohms max.
INDUCTANCE	3-1 10kHz, 100mVAC, Ls	1.80mH ±10%
SATURATION CURRENT	20% rolloff from initial	350mA
LEAKAGE INDUCTANCE	3-1 tie(4+5, 7+9), 100kHz, 100mVAC, Ls	20uH typ., 35uH max.
DIELECTRIC	3-7 tie(1+4), 4500VAC, 1 second	4500VAC, 1 minute
DIELECTRIC	3-4 1500VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-1):(4-5)	5.67:1, ±3%
URNS RATIO	(3-1):(7-9)	17:1, ±3%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

- ⑥B Designed to comply with the following requirements as defined by IEC61558-2-16, Amendment 1:
 - Reinforced insulation for a primary circuit at a working voltage of 400VDC.

⑥C * DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

⑥B Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.	
6D	9/23	Method: Tray		TRANSFORMER	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	750871013	
6C	6/23	PKG-0730					
6B	6/15	www.we-online.com/midcom					
6A	2/10	SEE REVISION SHEET FOR REVISION LEVEL					
					eiSos p/n: 750871013		SPECIFICATION SHEET 1 OF 1