



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6F D.C. RESISTANCE	1-3 @20°C	0.150 ohms ±15%
6F D.C. RESISTANCE	6-4 @20°C	0.224 ohms ±15%
INDUCTANCE	1-3 100kHz, 10mVAC, Ls	388uH ±30%
DIELECTRIC	1-6 3438VAC, 1 second	2750VAC, 1 minute
URNS RATIO	(6-4):(1-3)	1.7:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
- Functional insulation.

CURRENT RATING: 200mA

VOLTAGE - TIME: 9.44Vus (1-2)

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0895 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750315227
6F	11/21					
6E	12/20					
6D	7/17					
6C	7/16	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315227	SPECIFICATION SHEET 1 OF 1