

WE-PD2A SMD Power Inductor



7850	784 775 10 L: 10 μ H R _{DC} : 0.041 Ω I _R : 2.30 A I _{sat} : 2.95 A	784 775 112 L: 12 μ H R _{DC} : 0.042 Ω I _R : 2.18 A I _{sat} : 2.23 A	784 775 115 L: 15 μ H R _{DC} : 0.044 Ω I _R : 1.93 A I _{sat} : 2.20 A	784 775 118 L: 18 μ H R _{DC} : 0.053 Ω I _R : 1.89 A I _{sat} : 2.14 A	7850	784 775 122 L: 22 μ H R _{DC} : 0.065 Ω I _R : 1.76 A I _{sat} : 1.81 A	784 775 127 L: 27 μ H R _{DC} : 0.074 Ω I _R : 1.48 A I _{sat} : 1.62 A	784 775 133 L: 33 μ H R _{DC} : 0.130 Ω I _R : 1.35 A I _{sat} : 1.47 A	
	784 775 139 L: 39 μ H R _{DC} : 0.116 Ω I _R : 1.25 A I _{sat} : 1.33 A	784 775 147 L: 47 μ H R _{DC} : 0.134 Ω I _R : 1.17 A I _{sat} : 1.24 A	784 775 168 L: 68 μ H R _{DC} : 0.218 Ω I _R : 0.99 A I _{sat} : 1.05 A	784 775 182 L: 82 μ H R _{DC} : 0.248 Ω I _R : 0.90 A I _{sat} : 0.95 A		784 775 20 L: 100 μ H R _{DC} : 0.281 Ω I _R : 0.77 A I _{sat} : 0.86 A	784 775 215 L: 150 μ H R _{DC} : 0.467 Ω I _R : 0.60 A I _{sat} : 0.71 A	784 775 218 L: 180 μ H R _{DC} : 0.574 Ω I _R : 0.55 A I _{sat} : 0.57 A	
	784 775 222 L: 220 μ H R _{DC} : 0.614 Ω I _R : 0.51 A I _{sat} : 0.56 A	784 775 227 L: 270 μ H R _{DC} : 0.699 Ω I _R : 0.47 A I _{sat} : 0.51 A	784 775 239 L: 396 μ H R _{DC} : 1.151 Ω I _R : 0.38 A I _{sat} : 0.43 A	784 775 247 L: 470 μ H R _{DC} : 1.370 Ω I _R : 0.36 A I _{sat} : 0.38 A		1054	784 776 10 L: 10 μ H R _{DC} : 0.028 Ω I _R : 2.98 A I _{sat} : 3.24 A	784 776 118 L: 18 μ H R _{DC} : 0.043 Ω I _R : 2.36 A I _{sat} : 2.43 A	784 776 122 L: 22 μ H R _{DC} : 0.051 Ω I _R : 2.04 A I _{sat} : 2.07 A
	784 776 127 L: 27 μ H R _{DC} : 0.063 Ω I _R : 1.95 A I _{sat} : 1.98 A	784 776 133 L: 33 μ H R _{DC} : 0.083 Ω I _R : 1.78 A I _{sat} : 1.89 A	784 776 139 L: 39 μ H R _{DC} : 0.088 Ω I _R : 1.62 A I _{sat} : 1.80 A	784 776 147 L: 47 μ H R _{DC} : 0.095 Ω I _R : 1.45 A I _{sat} : 1.62 A			784 776 156 L: 56 μ H R _{DC} : 0.112 Ω I _R : 1.36 A I _{sat} : 1.53 A	784 776 168 L: 68 μ H R _{DC} : 0.138 Ω I _R : 1.19 A I _{sat} : 1.49 A	784 776 182 L: 82 μ H R _{DC} : 0.150 Ω I _R : 1.11 A I _{sat} : 1.17 A
	784 776 20 L: 100 μ H R _{DC} : 0.200 Ω I _R : 1.02 A I _{sat} : 1.10 A	784 776 212 L: 120 μ H R _{DC} : 0.243 Ω I _R : 0.94 A I _{sat} : 0.99 A	784 776 215 L: 150 μ H R _{DC} : 0.300 Ω I _R : 0.81 A I _{sat} : 0.90 A	784 776 218 L: 180 μ H R _{DC} : 0.320 Ω I _R : 0.76 A I _{sat} : 0.78 A			784 776 222 L: 220 μ H R _{DC} : 0.451 Ω I _R : 0.67 A I _{sat} : 0.77 A	784 776 233 L: 330 μ H R _{DC} : 0.750 Ω I _R : 0.52 A I _{sat} : 0.59 A	784 776 247 L: 470 μ H R _{DC} : 0.969 Ω I _R : 0.44 A I _{sat} : 0.50 A

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2011

www.we-online.com

All products
in stock!