



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



\* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	2-6 , 5.65 Ohms ±10%.
	3-7 , 1.70 Ohms ±10%.
DIELECTRIC RATING:	1000VAC, 1 minute tested by applying 1250VAC for 1 second between pins 2-3.
INDUCTANCE:	2.30 mH ±10%, 10kHz, 100mVAC, 0mADC, 2-6, Ls.
SATURATION CURRENT:	260mA saturating current that causes 20% rolloff from initial inductance.
TURNS RATIO:	( 2-6):( 3-7 ) , ( 4 ):(1.00) , ±1%.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

<b>WE-Midcom, Inc.</b> Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005 (.127mm)		<b>WE-Midcom, Inc.</b>	
	Drawing Title <h1>Transformer</h1>		Drawing Number <h2>7608000904</h2>	Rev. 01
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Spec Sheet 1 of 1
Engineer:PLP			01/05/2012	