


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 $\phi.031(8)$
 [.80]





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-4 @20°C	0.048 ohms ±20%
D.C. RESISTANCE	9-10 @20°C	0.060 ohms ±20%
INDUCTANCE	9-10 10kHz, 100mVAC, Ls	130uH ±5%
SATURATION CURRENT	9-10 20% rolloff from initial	13A
LEAKAGE INDUCTANCE	9-10 tie(3+4), 100kHz, 100mVAC, Ls	52uH typ., 75uH max.
DIELECTRIC	3-10 1500VAC, 1 second	-
URNS RATIO	(9-10):(4-3)	30:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1162 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE INDUCTOR	PART NO. 750315487
6A	3/18	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315487	SPECIFICATION SHEET 1 OF 1