


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes





6B

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	9-10 @20°C	0.240 ohms $\pm 10\%$
INDUCTANCE	9-10 10kHz, 100mVAC, Ls	600.00uH $\pm 10\%$
SATURATION CURRENT	9-10 20% rolloff from initial	8.5A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0825 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	DRAWING TITLE INDUCTOR	PART NO. 750318456
6B	3/20			Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]		
6A	10/19	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750318456	SPECIFICATION SHEET 1 OF 1

