

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes


more than you expect




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	0.12 ohms max.
D.C. RESISTANCE	6-4 @20°C	0.10 ohms max.
INDUCTANCE	3-1 10kHz, 100mV, Ls	150.00µH ±10%
SATURATION CURRENT	3-1 20% rolloff from initial	15A
DIELECTRIC	3-4 1500VAC, 1 second	
TURNS RATIO	(3-1):(6-4)	14:1



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 $\varnothing .039(5)$
 [1.00]



TERM. NO.'s FOR REF. ONLY



LOT CODE & DATE CODE



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C including temp rise.
 Current rating: 5A

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE INDUCTOR	PART NO. 750345199
DATE	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	PKG-0631				
REV.	01				
DATE	2022/9/28	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1