



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 98%, Cu 2%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.360 ohms max.
D.C. RESISTANCE	4-3 @20°C	0.590 ohms max.
INDUCTANCE	1-2 10kHz, 100mV, Ls	70µH min.
INDUCTANCE	4-3 10kHz, 100mV, Ls	135µH min.
DIELECTRIC	1-4 5000VDC, 1 second	
URNS RATIO	(4-3):(1-2)	1.46:1



GENERAL SPECIFICATIONS:  
 OPERATING TEMPERATURE RANGE: -20°C to +85°C.  
 STORAGE TEMPERATURE RANGE: -40°C to +105°C.  
 COPLANARITY: All 4 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1°      Decimals: ±.005 [.13] Fractions: ±1/64      Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750320415</b>
DATE	1/20/2023	Method: Tape & Reel		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	JJB	PKG-0548				
REV.	00					
DATE	3/28/2023	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1