



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	16-9 tie(11+14), @20°C	1.50 ohms max.
D.C. RESISTANCE	1-4 tie(1+2, 3+4), @20°C	0.200 ohms max.
D.C. RESISTANCE	5-8 tie(6+7), @20°C	1.20 ohms max.
INDUCTANCE	16-9 tie(11+14), 10kHz, 100mVAC, Ls	100uH ±7%
LEAKAGE INDUCTANCE	16-9 tie(11+14, 1+2+3+4, 5+6+7+8), 100kHz, 100mVAC, Ls	1.25uH max.
LEAKAGE INDUCTANCE	5-8 tie(6+7, 1+2+3+4, 9+11+14+16), 100kHz, 100mVAC, Ls	1.1uH max.
LEAKAGE INDUCTANCE	1-4 tie(1+2, 3+4, 5+6+7+8, 9+11+14+16), 100kHz, 10mVAC, Ls	50nH max.
INTERWINDING CAPACTTANCE	16-1 tie(11+14, 1+2, 3+4), 100kHz, 100mVAC, Cs	50pF max.
INTERWINDING CAPACTTANCE	16-5 tie(11+14, 6+7), 100kHz, 100mVAC, Cs	30pF max.
INTERWINDING CAPACTTANCE	1-5 tie(1+2, 3+4, 6+7), 100kHz, 100mVAC, Cs	40pF max.
DIELECTRIC	16-1 tie(11+14, 2+3, 4+5, 6+7), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(16-9):(1-4), tie(11+14, 1+2, 3+4)	4.25:1, ±2%
URNS RATIO	(16-9):(5-8), tie(11+14, 6+7)	1:1, ±2%
TOTAL HARMONIC DISTORTION	100kHz, Vgen of 3Vrms, 5.6 ohm load, 100 ohm input, tie(11+14, 1+2, 3+4)	-85dB max.
LONGITUDINAL BALANCE ¹	100k - 30MHz	35dB min.

¹Per ITU Method (L->M)

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Supplementary insulation for a primary circuit at a working voltage of 250Vrms.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

AGENCY NUMBER

UL CODE
FILE# E205930 AE

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT
		Method: Tape & Reel PKG-0739 www.we-online.com/midcom	
6A	3/11	SEE REVISION SHEET FOR REVISION LEVEL	

Tolerances unless otherwise specified:
Angles: ±1°
Decimals: ±.005 [.13]
Fractions: ±1/64 Footprint: ±.005 [.13]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER
eiSos p/n: 750510364

PART NO.
750510364
SPECIFICATION SHEET 1 OF 1

