




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 tie(2+3), @20°C	0.720 ohms max.
D.C. RESISTANCE	8-5 tie(6+7), @20°C	1.40 ohms max.
INDUCTANCE	1-4 tie(2+3), 100kHz, 100mVAC, Ls	400uH ±10%
LEAKAGE INDUCTANCE	1-4 tie(2+3, 5+6+7+8), 1MHz, 100mVAC, Ls	900nH max.
INTERWINDING CAPACITANCE	1-8 tie(1+2+3+4, 5+6+7+8), 10kHz, 100mVAC, Cp	35pF max.
DIELECTRIC	1-8 tie(2+3, 6+7), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(1-4):(8-5), tie(2+3, 6+7)	1:1, ±2%
URNS RATIO	(1-3):(8-6)	1:1, ±2%
TOTAL HARMONIC DISTORTION	50kHz, 3.5Vrms across 100 ohm load on PRI, Vgen to SEC through 100 ohm input, tie(2+3, 6+7)	-66dB max.



**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +85°C.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Basic insulation for a primary circuit at a working voltage of 250Vrms.

⑥ Designed to meet K.21, 6kV (10 x 700usec, 5± repetitions) surge test between PRI and SEC.


Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

⑥C

AGENCY NUMBER	
UL60950-1	E205930
CSA60950-1 (Via CUL)	E205930

REV.	DATE	Packaging Specifications
6D	7/17	Method: Tape & Reel
6C	11/16	PKG-0987
6B	9/15	www.we-online.com/midcom
6A	6/14	SEE REVISION SHEET FOR REVISION LEVEL



Tolerances unless otherwise specified:  
Angles: ±1°  
Fractions: ±1/64  
Decimals: ±.005 [.13]  
Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

**TRANSFORMER**

eiSos p/n: 750510540



PART NO.

**750510540**

SPECIFICATION SHEET 1 OF 1