



ROHDE & SCHWARZ

Make ideas real



1

Design for EMI Troubleshooting and Debugging EMI failures

ROHDE & SCHWARZ

Make ideas real




2

AGENDA

- ▶ EMC Standards Overview
- ▶ Traditional EMI Test
 - Compliance test with a EMI Test Receiver
- ▶ EMI Debug and Troubleshooting
 - Troubleshooting with a spectrum analyzer
 - Troubleshooting with a oscilloscope
- ▶ Measurement solution comparison

First pass compliance test:
Devices can have a **90% failure rate**



■ Pass ■ Fail

Source: EETimes.com, "IoT Devices: Most initially Fail EMI testing"

3



Image Credit: Timothy Colegrove
CCA-SA

Design for EMI

EMI is not new


- ▶ Faster Clocks
- ▶ Smaller Form Factors
- ▶ RF Sources
- ▶ High frequency switching supplies
- ▶ Plastic vs Metal Housing



4

EMI CONSIDERATIONS FOR YOUR DESIGN

- Specify known frequency source (clock and etc.)
- Generate a list of possible harmonic frequencies
- Determine the frequency of switching powers supplies
- Identify miscellaneous periodic waves



Causes of EMI

EMI is often caused by switching of signals:

- Power Supply
- Clocks
- DDR memory interface
- etc.

These are referred to as narrowband interference and generally occurs at very specific frequencies related to components on your board.



Rohde & Schwarz

Design for EMI

5

APPLICATION EXAMPLE: POWER SUPPLY DESIGN COMPLIANCE




RT06



Pre-compliance



Test Receiver



Compliance




6 Rohde & Schwarz

Design for EMI

6

APPLICATION EXAMPLE: OPTIMIZING WIDE BAND-GAP SWITCHING



7 Rohde & Schwarz


Design for EMI

7

EMC Standards and background

8

WHAT IS EMC?



9

Rohde & Schwarz

Design for EMI

9

STANDARDS

International Electrotechnical Commission (IEC)

Comité International Spécial des Perturbations Radio (CISPR)




10


Rohde & Schwarz

Design for EMI

10



11




13

EMI Testing Traditional Approach

14

SYSTEM CONFIGURATION




15 Rohde & Schwarz

Design for EMI

15

CONDUCTED EMISSIONS TEST (AC MAINS)




16 Rohde & Schwarz

Design for EMI

16

RADIATED EMISSIONS TEST





17 Rohde & Schwarz

Design for EMI

17

ELEKTRA: PC Software for better automation, reporting




FSx-K54: EMI Measurement Application

EMI SCAN WITH A TEST RECEIVER

- ▶ Full compliance means full chamber, CISPR 16 compliant receiver
- ▶ Want results that will match these
- ▶ Start with the limit lines for the standard you are testing against
- ▶ Finding a quiet area is more and more challenging
- ▶ Consider use of a full compliance chamber

18

COMPLIANCE EMC TESTING: MEASURING EQUIPMENT TRANSDUCERS



Antenna – electric radiated emission



Antenna – magnetic radiated emission



Artificial Network – Conducted voltage



ISN - Conducted voltage



Current probe – conducted current



Absorbing clamp – disturbance power




19 Rohde & Schwarz

Design for EMI

19

EMC STANDARDS VS EMI MEASUREMENTS



Typical EMC Measurement

- ▶ Mostly far field in nature
- ▶ More accurate with less ambience noise
- ▶ More expensive to setup



Near Field Probe



EMI Measurement with Scope or Spectrum Analyzer

- ▶ Near field measurements
- ▶ More noise and less accurate
- ▶ Cheap and flexible



20 Rohde & Schwarz




Design for EMI

20

EMI Testing Debugging and troubleshooting

21

BASIC EMI DEBUG PROCESS




22 Rohde & Schwarz

Design for EMI

22


Near Field Probe Types



23

Design for EMI

23



NEAR FIELD PROBING

- ▶ Check for EMI issues periodically to make sure no obvious issues
- ▶ Can use a Spectrum Analyzer or Scope with 50 Ohm Input
- ▶ Scopes with 1 mV/div settings do not need pre-amplifier

24

Choosing an approach

25

SPECTRUM ANALYZER OR OSCILLOSCOPE FOR EMI DEBUGGING




26 Rohde & Schwarz

Design for EMI

26


Laptop
Power Supply



TROUBLESHOOT WITH A SPECTRUM ANALYZER

- ▶ DUT is a switching power supply
- ▶ Looking for “offending” signals that would fail a standards based limit line
- ▶ **Step 1:**
Hunt for the offending signals – use markers to find the highest power levels in the spectrogram (lower display)


27



TROUBLESHOOT WITH A SPECTRUM ANALYZER

- ▶ **Step 2:**
Use Zero Span at the same frequency the offending signal occurs
– 19.4 MHz in this case
- ▶ Zero span shows the RF envelope power
- ▶ Use markers to measure the time between pulses (clock signal) – 1.6 msec in this case

28





TROUBLESHOOT WITH A SPECTRUM ANALYZER

- ▶ **Step 3:**
Spectrum display
Set Sweep time to >1000x the measured time interval (1.6 msec)
- ▶ 1000x ensures enough points in the spectrum trace display to see the “pulse”
- ▶ (Or use a real time spectrum analyzer)
- ▶ This is the worst case signal: actual quasi-peak detector might show a lower level
- ▶ Work to address this offending emission

29

QUASI PEAK DETECTOR

- ▶ Quasi-peak means 'not quite peak', or 'aiming towards peak but not actually peak'
- ▶ Quasi-peak detector was believed to better indicate the subjective annoyance level experienced by a listener hearing impulsive interference to an AM radio station



Spectrum analyzers and EMI receivers
both have a quasi-peak detector



30 Rohde & Schwarz

Design for EMI

30

IMPORTANT SCOPE-PARAMETERS FOR EMI DEBUGGING

Bandwidth	100 MHz to 4 GHz	Analog capture range of the EMI signals
Sample rate	> 2X Analog BW	Max FFT Frequency is half the sample rate
Coupling	50 Ohm	Near Field Probes are designed for 50 Ohm systems
Vertical sensitivity	1 – 5 mV/div	Check HW settings, larger requires a pre-amplifier
FFT Span / RBW	Span to Resolution bandwidth factor (100 – 1000)	
FFT gating	Easily isolate spurious spectral components in time domain	
FFT Zone Trigger	Draw a mask or area on an FFT to trigger the oscilloscope	



31 Rohde & Schwarz

Design for EMI

31

MODERN SCOPE FFT CAPABILITIES CORRELATION OF TIME AND FREQUENCY INFORMATION



32 Rohde & Schwarz

Design for EMI

32

MODERN SCOPE FFT CAPABILITIES CORRELATION OF TIME AND FREQUENCY INFORMATION





33 Rohde & Schwarz

Design for EMI

33

OBSERVE THE SPECTRUM WHILE SCANNING WITH A NEAR-FIELD PROBE





34

Rohde & Schwarz

Design for EMI

34

OBSERVE THE SPECTRUM WHILE SCANNING WITH A NEAR-FIELD PROBE





35

Rohde & Schwarz

Design for EMI

35

OBSERVE THE SPECTRUM WHILE SCANNING WITH A NEAR-FIELD PROBE




36 Rohde & Schwarz

Design for EMI

36

MODERN SCOPE FFT CAPABILITIES MASK TEST / ZONE TRIGGER



User-defined
spectrum mask



"Stop-on-violation"
function



Analyze underlying source





37 Rohde & Schwarz

Design for EMI

37

FFT GATE SPECIFIC MOMENTS IN TIME



EMI RECEIVER, SPECTRUM ANALYZER AND OSCILLOSCOPE

Feature	EMI Receiver	Spectrum Analyzer	Oscilloscope
General purpose RF	-	✓	✓
Wireless standards WLAN, IOT, Cellular	-	✓	✓
Serial data bus decode	-	-	✓
EMI detectors / bandwidths (incl. QP)	✓	✓	-
EMI Meas. Dynamic Range & Sensitivity	Very high / Very high	High / Very high	Medium
Log-scale & limit lines	✓	✓	(✓)
Scan Types	All (Sweep, step, time-domain, zero-span)	Some (Sweep, zero-span)	No scan
Time/frequency correlation possible	✓	✓	✓
Gapless recording	Very long	Long	Medium
Auto ranging	✓	-	-

R&S Solutions

40

R&S SOLUTIONS FOR EMI FROM R&D TO FINAL CONFORMANCE TEST

Oscilloscopes

- ▶ From 50 MHz Handheld to high performance 16 GHz
- ▶ Integrated instruments: logic analyzer, protocol decoder, arbitrary waveform gen, TDR
- ▶ MXO4/MXO5, RTO6, RTP




Test Receiver/Spectrum Analyzers

- ▶ Full line up from high performance to economy class and handheld



Accessories to EMC Systems

- ▶ From Near Field Probes, antennas and LISNs to full test chambers & EMC Receivers



41 Rohde & Schwarz

Design for EMI


41

SUMMARY

1. EMI is complex but can be tested easily
2. Test EMI early in the design process
3. Oscilloscopes and Spectrum Analyzers can be used for EMI debugging

R&S has full product portfolio from probes to chambers with technical experts to help!

First pass compliance test:
Low cost IOT device
90% failure rate



Source: Eetimes.com, "IoT Devices: Most initially Fail EMI testing"