

WE Backup Your Application Hot Swappable Supercapacitor Backup Solution

Frank Puhane


Leader Technical Engineering
eiCap / eiRis Capacitors & Resistors Division

Agenda

- **Short roundup about Supercapacitors**
 - Classification of Supercapacitors
 - Model parameters and performance
 - Charge-, discharge and frequency behavior
- **WE Backup Your Application**
 - Hot Swappable Supercapacitor Backup Solution
 - Overview and general information
 - Design-in process and lifetime
 - Performance of the complete solution



Classification of Capacitors



Types of Supercapacitors based on design of electrodes:

- **Double layer capacitors**
 - Electrodes: carbon or carbon derivatives
- **Pseudocapacitors**
 - Electrodes: oxides or conducting polymers (high faradaic pseudocapacitance)
- **Hybrid capacitors**
 - Electrodes: special electrodes with significant double-layer capacitance and pseudocapacitance

Supercapacitors vs. Batteries and Capacitors



Capacitors

- **Very fast charging** and discharging ($\ll$ sec)
- Very high power output
- Very low energy capacity



Supercaps




- **Fast charging** and discharging (min – sec)
- High life cycle ($\approx$ 500,000 cycles)
- High power output
 - $\approx$ 10 times higher than Li-ion battery
- Low energy capacity
 - $\approx$ 30 times lower than Li-ion battery
- Energy: 0.002 Wh – 0.04 Wh
- Power: 36 W – 90 W



Batteries

- **Long charging** time (hours)
- High energy capacity
- Low power output
- Energy: 1.4 Wh
- Power: 6 W


Structure of the Supercapacitor



Parameter and Performance

Basic Parameters:

- U_r , **Rated Voltage**:
 - is not determined by the equivalent circuit but by electrochemistry (Decomposition Voltage)
 - Non-Aqueous Electrolyte (typ.): $\approx 2\text{ V} \dots 3\text{ V}$
 - Aqueous Electrolyte (typ.): $\approx 1.5\text{ V}$



- $C \Rightarrow$ **Capacitance**
- $R_{ESR} \Rightarrow$ **ESR**
- $R_{Leak} \Rightarrow$ **Leakage**
 - Influence on charge storing capabilities ($R_{Leak} \approx 10\text{ k}\Omega \dots 1\text{ M}\Omega$)

Performance Parameters:

- **Energy storage capacity:**

$$E = \frac{1}{2} \times C \times U_r^2$$


- **Maximum Power output:**

$$P_{max} = \frac{U_r^2}{4 R_{ESR}}$$

- **Characteristic R-C Time:**

$$\tau = R_{ESR} \times C$$

Charge and Discharge Behavior



Agenda


- Short roundup about Supercapacitors
 - Classification of Supercapacitors
 - Model parameters and performance
 - Charge-, discharge and frequency behavior
- **WE Backup Your Application**
 - Hot Swappable Supercapacitor Backup Solution
 - Overview and general information
 - Design-in process and lifetime
 - Performance of the complete solution



LTC3351 – Overview



- Hot Swappable Supercapacitor Backup Solution
- **WE** want 30W for 15sec. (12V @ 2.5A) at the output
- Why we use LTC3351?
 - Integrated hot swap controller with circuit breaker
 - High efficiency synchronous step-down CC/CV charging of one to four series Supercapacitors
 - Step-up mode in backup provides greater utilization of stored energy in Supercapacitors
 - 16-bit ADC for monitoring system voltages/currents, capacitance, and ESR
 - Contains an I2C/SMBus compatible port allows communication with the LTC3351 for configuration and reading back telemetry data



What is Hot Swap / Hot Plug



■ Hot Swapping

- Replacing or adding components
- No shutdown or stopping of the running system
- No interruption to the system
- Pre-Charging thru special pins
- Current limiter or soft start can protect the circuit

■ Hot Plug



- Hot plugging describes only the addition of components that would expand the system
- No significant interruption to the system




Specification of the Application



- 24V input to output rail
- Step-Up mode V_{out}
 - $V_{out} = 12\text{ V}$
- Step-Down mode V_{CAP}
 - 4 Supercapacitors
 - $V_{CAP} = 10.6\text{ V}$
- No direct supply from V_{CAP}
 - $V_{CAP} < V_{out}$
- f_{sw}
 - 450 kHz
- Input current limit
 - $I_{max_charge} = 2,5\text{ A}$
- Constant Power Discharge
- Supply the load and charge the Supercapacitor



LTC3351 Hot Swap / Hot Plug



3351 F01

How to Choose the Supercapacitor



- Backup is defined due to the application
- The four steps of design-in
 - Choose the mode of discharge
 - Constant Power
 - Calculate the capacitance (operating time, output power, output current)
 - 30 W => 12 V @ 2.5 A for 15 sec.
 - $E = P \cdot t = 30 \text{ W} \cdot 15 \text{ s} = 450 \text{ J}$
 - $C = 2 \cdot \frac{E}{V_1^2 - V_2^2} = 2 \cdot \frac{450 \text{ J}}{10.6 \text{ V}^2 - 2 \text{ V}^2} = 4.2 \text{ F}$
 - Identify the suitable charging process
 - Constant Current, Constant Power and Constant Voltage
 - Calculate charging current
 - Highest possible current for the LTC3351 => 6,4A


Choosing the right Supercapacitor




- **WE** use 50F / 2.7V Supercapacitor radial type 850617022002
 - <https://redexpert.we-online.com/redexpert/#!/smodule/39>




Impedance/Frequency



ESR/Frequency




Maintain Voltage over Time (precharge 2.7V @ 20°C)



Supercapacitor Bank




- 4 Supercapacitors in series connection
- $E_{\text{total}} = \frac{1}{2} * C_{\text{total}} * U_{\text{VCAP}}^2$
 - $C_{\text{total}} = 12,5 \text{ F}$
 - $U_{\text{VCAP}} = 10.6 \text{ V}$
 - $\Rightarrow E_{\text{total}} = 702.25 \text{ J}$
- Max. Power = $U_r^2 / 4 * (4 * \text{ESR})$
 - $V_{\text{CAP}} = 10.6 \text{ V}$
 - ESR for one Supercapacitor = $2.23 \text{ m}\Omega$
 - Max. Power = 3053 W
- No balancing on board required
 - LTC3351 integrated active stack balancer
- Additional circuitry is for discharging the bank



Supercapacitor Bank



- 4 Supercapacitors in series connection
- $E_{\text{total}} = \frac{1}{2} * C_{\text{total}} * U_{\text{VCAP}}^2$
 - $C_{\text{total}} = 12,5 \text{ F}$
 - $U_{\text{VCAP}} = 10.6 \text{ V}$
 - ⇒ $E_{\text{total}} = 702.25 \text{ J}$
- **Max. Power = $U_r^2 / 4 * (4 * \text{ESR})$**
 - $V_{\text{CAP}} = 10.6 \text{ V}$
 - **ESR for one Supercapacitor = 2.23 mΩ**
 - **Max. Power = 3053 W**
- **No balancing on board required**
 - LTC3351 integrated active stack balancer
- **Additional circuitry is for discharging the bank**






Balancing of Supercapacitor

■ Worst Case Example:

- Two in series connected capacitors with a rated capacitance of 10 F (tol.: -10%, +30%)
- Rated voltage of 2.7 V are charged at 5.4 V

■ Following equations are need for the calculations:

- $U_g = U_1 + U_2$
- $U_2 = \frac{q}{C_2}$ and $U_1 = \frac{q}{C_1}$





- $\rightarrow U_1 = \frac{5.4 \text{ V}}{(1.44+1)} = \mathbf{2.21V}$
- $\rightarrow U_2 = \frac{5.4 \text{ V}}{\left(\frac{1}{1.44}+1\right)} = \mathbf{3.19V}$ (Caution, Overvoltage!)

Lifetime of Supercapacitor



- Supercapacitors lose capacitance as they age
- ESR will rise over the lifetime




Lifetime of Supercapacitor



- Lifetime for 4 Supercapacitors in series
- $V_{CAP} = 10.6 \text{ V}$
 - Voltage on a single cell $\Rightarrow 2.65 \text{ V}$
- Defined Mission Profile
 - Max. Temp = $40 \text{ }^{\circ}\text{C}$
 - Max. Voltage = 2.65 V
- We use 4 * 50 F Supercapacitors in series
 - $C_{total} = 12.5 \text{ F}$
 - With a tolerance of -10% $\Rightarrow C_{total} = 11.25 \text{ F}$
- After 12 years $\Rightarrow C_{total} = 5.6 \text{ F}$
 - Calculated capacitance 4.2 F
 - Lifetime definition -30% capacitance and 2x ESR
- Lifetime depends on voltage and temperature
- Current increases self heating


Mission Profile			
Time [h]	Temp. [$^{\circ}\text{C}$]	Voltage [V]	Model
10	40	2.65	DC Voltage Model
2	40	1.	DC Voltage Model
6	25	0	DC Voltage Model
6	25	0	DC Voltage Model



Lifetime of Supercapacitor


- Same Mission Profile
- Different cell voltage with 2.3 V

Mission Profile			
Time [h]	Temp. [°C]	Voltage [V]	Model
10	40	2.3	DC Voltage Model
2	40	1.	DC Voltage Model
6	25	0	DC Voltage Model
6	25	0	DC Voltage Model



- Same Mission Profile
- Different temperature at the Supercapacitor with 65 °C


Mission Profile			
Time [h]	Temp. [°C]	Voltage [V]	Model
10	65	2.65	DC Voltage Model
2	65	1.	DC Voltage Model
6	25	0	DC Voltage Model
6	25	0	DC Voltage Model





Backup Solution




Backup ca. 15sec
Uout 120V/30W




Backup Solution




Backup Solution Real World




Performance Charging with Load



Performance Charging without Load




Performance Charging / Discharging




Design and Application Review



- Backup solution with a size of 10 cm x 18.5 cm
 - 3.94 inch x 7.3 inch
- Input voltage 24V / backup voltage 12 V
- Output power 30 W => 12 V @ 2.5 A
- Support Note for design-in process
- We are currently working on an evaluation kit from WE
- **WE** support you in your design





Questions

& Answers

We are here for you now!
Ask us directly via our chat or via E-Mail.

exhibition@we-online.com